



RATINGS:

CURRENT: 10 AMPS
 BREAKDOWN VOLTAGE: 5700 V RMS
 CONTACT RESISTANCE: 0.010 OHMS MAX.
 CONTACT-TO-PANEL C: 2 pF NOMINAL

THIS DOCUMENT IS THE PROPERTY OF
 KEYSTONE ELECTRONICS CORP. AND
 SHALL NOT BE REPRODUCED, DISTRIBUTED
 OR USED AS A BASIS FOR MANUFACTURE
 WITHOUT PRIOR WRITTEN PERMISSION
 FROM KEYSTONE ELECTRONICS CORP.



NOTES:

1. CONTACT:
 MAT'L - PHOSPHOR BRONZE,
 TIN PLATE.
 BODY:
 MAT'L - NYLON 6/6 PER ASTM D4066
2. NUT: BRASS, NICKEL PLATED,
 SUPPLIED UNASSEMBLED.

| PART NO. | COLOR |
|----------|--------|
| 6018 | WHITE |
| 6019 | RED |
| 6020 | BLACK |
| 6021 | GREEN |
| 6022 | YELLOW |
| 6023 | BLUE |

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

INSULATED TIP JACK

MATERIAL

AS NOTED

FINISH

AS NOTED

DRN BY

BOONE

DATE 12.10.82

APP'D

LN

SCALE 2X

TOLERANCES

INCH [MM]

[MM]

DECIMAL

± .010

[± 0.25]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

6018-6023

| | | |
|---------|--------------------------|------|
| 4.12.12 | CHANGE AS PER ECN 12-045 | D |
| 2.18.11 | CHANGE AS PER ECN 11.018 | C |
| 4.23.10 | CHANGE AS PER ECN 10-030 | B |
| 2.5.03 | CHANGE AS PER ECN 03-010 | A |
| DATE | DESCRIPTION | REV. |