





D

C


B

A



PC BOARD LAYOUT

- 1 HOUSING MATERIAL: GLASS-FILLED POLYESTER. COLOR: GRAY.
- 2 POST MATERIAL: PHOSPHOR BRONZE.
- 3 POST FINISH: DIN 41612 CLASS 3 IN CONTACT AREA. TIN-LEAD PLATE ON POSTS.
- 4 POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN-LEAD PLATE ON POSTS.
- 5 ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK PC BOARD. RECOMMENDED PC BOARD HOLES ARE Ø1.151 [.0453] PLATED THROUGH WITH 0.02-0.08 [.001-.003] COPPER AND 0.008 [.0003] MIN TIN-LEAD PLATING. FINISHED HOLE AFTER PLATING, Ø0.94-1.09 [.037-.043].
- 6 PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA.
- 7 MARKING ON THIS SIDE.



|          |                  |             |   |   |   |                        |                  |
|----------|------------------|-------------|---|---|---|------------------------|------------------|
| OBSOLETE | 3                | 1-16        | X | - | X | 32                     | 650931-9         |
| OBSOLETE | 4                | 1-16        | X | - | X | 32                     | 650931-5         |
|          | 4                | 1-16        | X | - | X | 32                     | 650931-4         |
| NOTES    | POSITIONS LOADED | ROWS LOADED | C | B | A | NO. OF LOADED POSITION | ASSY PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± 0.13 [.005]  
4 PLC ± -  
ANGLES ± -

MATERIAL

FINISH

DWN  
L. BRINER  
3/18/91

CHK  
D.C. RUBENDALL  
3/26/91

APVD  
D.C. RUBENDALL  
3/26/91

tyco  
Electronics

Tyco Electronics Corporation  
Harrisburg, PA 17105-3608

NAME

ASSEMBLY, PIN, VERTICAL, EUROCARD, TYPE 1/2R, SELECT LOAD, ROWS A AND C, 32/48 POSITION, 6.35 [.250] PRESS-IT POSTS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

—

A1

00779

650931

—

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV L