


March 30, 2000-14

Recommended Operating Conditions



Both relays on with equal load currents.
For a single relay operation, refer to LH1501 Recommended Operating Conditions graph.

Absolute Maximum Ratings, $T_A=25^\circ\text{C}$

Stresses in excess of the absolute Maximum Ratings can cause permanent damage to the device. These are absolute stress ratings only. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute Maximum Ratings for extended periods of time can adversely affect reliability.

Ambient Temperature Range (T_A)		-40 to +85°C
Storage Temperature Range (T_{stg})		-40 to +150°C
Pin Soldering Temperature ($t=10$ s max) (T_S)		260°C
Input/Output Isolation Voltage ($t=1.0$ s, $I_{ISO}=10$ μA max) (V_{ISO})		5300 V_{RMS}
Pole-to-Pole Isolation Voltage (S1 to S2)* (dry air, dust free, at sea level)		1600 V
LED Continuous Forward Current (I_F)		50 mA
LED Reverse Voltage ($I_R \leq 10$ μA) (V_R)		8.0 V
DC or Peak AC Load Voltage ($I_L \leq 50$ μA) (V_L)		350 V
Continuous DC Load Current (I_L)		
One Pole Operating		150 mA
Two Poles Operating		110 mA
Peak Load Current ($t=100$ ms) (single shot) (I_P)		400 mA
Output Power Dissipation (continuous) (P_{DISS})		600 mW

* Breakdown occurs between the output pins external to the package.

Electrical Characteristics, $T_A=25^\circ\text{C}$

Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

Parameter	Sym.	Min.	Typ.	Max.	Units	Test Conditions
Input						
LED Forward Current, Switch Turn-on	I_{Fon}	0.2	0.9	—	mA	$I_L = \pm 150$ mA, $t=10$ ms
LED Forward Current, Switch Turn-off	I_{Foff}	—	1.0	2.0	mA	$V_L \pm 300$ V
LED Forward Voltage	V_F	1.15	1.22	1.45	V	$I_F=10$ mA
Output						
ON-resistance	R_{ON}	12	20	25	Ω	$I_F=0$ mA, $I_L=50$ mA
OFF-resistance	R_{OFF}	0.1	1.4	—	G Ω	$I_F=5.00$ mA, $V_L = \pm 100$ V
Off-state Leakage Current	—	—	0.07	1.0	μA	$I_F=5.0$ mA, $V_L = \pm 100$ V
		—	0.08	1.0	μA	$I_F=5.0$ mA, $V_L = \pm 350$ V
Output Capacitance	—	—	35	—	pF	$I_F=5.0$ mA, $V_L=1.0$ V
		—	10	—	pF	$I_F=5.0$ mA, $V_L=50$ V
Pole-to-Pole Capacitance	—	—	0.5	—	pF	$I_F=0$ mA
Switch Offset	—	—	0.1	—	μV	$I_F=0$ mA
Transfer						
Input/Output Capacitance	C_{ISO}	—	1.1	—	pF	$V_{ISO}=1.0$ V
Turn-on Time	t_{on}	—	2.0	3.0	ms	$I_F=5.0$ mA, $I_L=50$ mA
Turn-off Time	t_{off}	—	1.0	3.0	ms	$I_F=5.0$ mA, $I_L=50$ mA

Typical Performance Characteristics

Figure 1. LED Voltage vs. Temperature




Figure 4. On-resistance vs. Temperature




Figure 2. LED Dropout Voltage vs. Temperature




Figure 5. Switch Capacitance vs. Applied Voltage




Figure 3. LED Current for Switch Turn-off vs. Temperature




Figure 6. Output Isolation




Figure 7. Insertion Loss vs. Frequency




Figure 10. Leakage Current vs. Applied Voltage at 70°C




Figure 8. Leakage Current vs. Applied Voltage at 25°C




Figure 11. Leakage Current vs. Applied Voltage at 85°C




Figure 9. Leakage Current vs. Applied Voltage at 50°C




Figure 12. Switch Breakdown Voltage vs. Temperature




Figure 13. Switch Offset Voltage vs. Temperature




Figure 16. Turn-off Time vs. LED Current




Figure 14. Turn-on/off Time vs. Temperature




Figure 15. Turn-on Time vs. LED Current

