



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT By -- ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
DW	P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A		RELEASED	24AUG2011	V.P.	H.K.	

2129318-1: AS SHOWN



⑤	TINE PLATE	HIGH TEMP THERMOPLASTICS, COLOR:BLACK, UL94 V-0		1
④	PEG	COPPER ALLOY	Sn PLATE AT SOLDERING AREA UNDER NICKEL PLATE ALLOVER	2
③	LOWER CONT	COPPER ALLOY	Au PLATE (10 u") AT CONTACT POINT	26
②	UPPER CONT	COPPER ALLOY	Sn PLATE AT SOLDERING AREA UNDER NICKEL PLATE ALLOVER	26
①	HOUSING	HIGH TEMP THERMOPLASTICS, COLOR:BLACK, UL94 V-0		1
NO	DESCRIPTION	① MATERIAL	② FINISH	QTY.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.25
1 PLC ± 0.25
2 PLC ± 0.25
3 PLC ± 0.25
4 PLC ± 0.25
ANGLES ± 3°

FINISH

DWN V.PENG 12JUL2010
CHK H.KODAMA 12JUL2010
APVD H.KODAMA 12JUL2010

PRODUCT SPEC
108-99028
APPLICATION SPEC

WEIGHT 3.8 GRAM

CUSTOMER DRAWING

TE Connectivity

NAME

MINICARD CONNECTOR
OFFSET MOUNT TYPE

SIZE A3
CAGE CODE
DRAWING NO C-2129318
RESTRICTED TO

SCALE 4:1
SHEET 1 OF 3
REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

— SEE SHEET 1

—



—

—

4. -D- IS THE TOP SURFACE OF PCB.

5 SCREWS ARE PREPARED BY CUSTOMER.

MODULE CARD
INSERTION DIRECTION




RECOMMENDED P.C.BOARD LAYOUT
(COMPONENT SIDE)
TOLERANCE:±0.05

HALF MINI CARD	23.9
FULL MINI CARD	48.05
DIMENSION	A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.05
1 PLC ± 0.05
2 PLC ± 0.05
3 PLC ± 0.05
4 PLC ± 0.05
ANGLES ± 1°

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

MINICARD CONNECTOR
OFFSET MOUNT TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2129318

SCALE 4:1

SHEET 2 OF 3

REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN


APVD

- SEE SHEET 1


-

-

-




SECTION B-B



SECTION A-A

A	170°~180°
F	0.1N~1.3N

PULL OUT



6. MATERIAL :

6.1 REEL: PS(RoHS) BLUE.

6.2 COVER TAPE: PE

6.3 SHIPPING BOX: CORRUGATED FIBER


7. QUANTITY :

7.1 PRIMARY PACKING: 800 PCS/REEL

7.2 SECONDARY PACKING: 3 REELS(2400PCS)/BOX

8. PEELING RESISTANCE: SEE TABLE

9. PEELING SPEED: 300mm/MINUTES.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

MINICARD CONNECTOR
OFFSET MOUNT TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

C-2129318


SCALE 4:1

SHEET 3 of 3

REV A

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± 0.25
1 PLC ± 0.25
2 PLC ± 0.25
3 PLC ± 0.25
4 PLC ± 0.25
ANGLES ± 3°

MATERIAL

FINISH