





Alcoa Fastening
Systems

DATA SHEET



.45 in. = 11 mm
.84 in. = 21 mm
1.00 in. = 25 mm
1.63 in. = 41 mm
2.25 in. = 57 mm
3.23 in. = 83 mm



REPLACEMENT PARTS

REF	PART NO.	REQ	DESCRIPTION
1	116156	1	Anvil - Driving -06
2	116158	1	Anvil - Driving -08
3	114873	1	Anvil Holder
4	114874	1	Collet
5	116299	1	Gripper Jaws
6	115742	1	Follower/pintail Tube Assembly
7	115741	1	Washer
8	505392	1	Spring (Lee #LC-051G-7)
9	115740	1	Sleeve
10	114739	1	Jam Nut

SEE OTHER SIDE FOR NOTES AND ASSEMBLY INSTRUCTIONS

99-1454	
NOSE ASSEMBLY	
Alcoa Fastening Systems Commercial Products 1 Corporate Drive - Kingston, NY 12401	OTHER
TYPE: Blind Rivet, Convertible FOR: MAGNA-LOK -06 & -08 TOOL: Avdel 7498	PRODUCT REVISION: 5-84 REVISED: 9/19/01