



main menue

- home
- products
- skills
- download
- online catalogue T&M
- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - 2 mm system
 - 2 mm safety system
 - 4 mm system
 - 4 mm safety system
- sets
- miscellaneous
- company
- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ sockets ▶ 4 mm safety system ▶ sockets ▶ 4 mm safety system ▶ SEP 2630 S1,9

SEP 2630 S1,9

datasheet for SEP 2630 S1,9
article number: 972363100



View Full-Size Image



product description:	order number: 972 363-100
description:	Gold-plated brass safety press-in socket, 4 mm diameter, contact-protected, with 1.9 mm soldering spike. For installation into switchpanels with wall thicknesses between 1 mm and 10 mm. Accessory BES 1000. Installation hole: 12.2 +/-0.1 mm diameter. Entry chamfer 0.5 x 45 degree.
typ:	SEP 2630 S1,9 schwarz/black
system:	4mm safety system
order number:	972 363-100
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
norm	IEC 61010
type of contact:	4 mm socket (unsprung)
type of termination:	solder
rated voltage:	AC/DC 1000 V
rated current: Please consider derating curve!	24 A
contact resistance:	5 mOhm
mounting:	moulded in
material	
contact material:	brass
contact surface material:	gold
housing material:	PA
environmental conditions:	
temperature range:	-40 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	

search online catalogue

Search

Search

Messetermine

No events

Newsletter Anmeldung

☒ Test & Measurement

First Name Name

E-mail

Subscribe

QR-Code

