

6

PIN	STYLE	MATING
01		5.9
02		8
03		9.9
04		11.4
05		9.2
06		10.4
07		5.3
09		17.00
10		8.10
11		8.50
12		3.05
13		14.35
14		4.00

PLATING


1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

4 = 2µm TIN MIN FULL PLATED

5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

– 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS



mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
N	F08-0253	LMU	08.12.10	angles	linear	mm	UNSHR.HEADER
P	B-18789	LMU	14.09.11				DR SMT
R	B-18983	LMU	14.10.03			scale N/A	
S	B-20276	LMU	15.02.16	dr	D.LE	01.01.24	dwg no
T	B-20561	AMA	15.03.26	enr	JM.C	01.01.24	sheet 2 of -
				chr	JM.C	01.01.24	size
				appd	JF.N	01.01.24	A3
sheet index	revision sheet						type
							CUSTOMER Drawing