


KU5N12

OUTLINE DIMENSIONS



RATINGS


●Absolute Maximum Ratings

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-40~125	℃
Junction Temperature	T _j		125	℃
Operating Temperature	T _{op}		-40~70	℃
Maximum Off-State Voltage	V _{DRM}		100	V
Surge On-State Current	I _{TSM}	Pluse-waveform 10/1000 μ s, Non-repetitive	50	A


●Electrical Characteristics (T_c=25℃)

Item	Symbol	Conditions	Ratings	Unit
Breakover Voltage	V _{BO}	dv/dt=8V/ms (Peak hold)	Min 110	V
Off-State Current	I _{DRM}	V _D = V _{DRM}	Max 5	μ A
Holding Current	I _H	Pulse measurement	Min 150(100)	mA
On-State Voltage	V _T	I _T = 2A	TYP 1.25	V
Capacitance	C _j	f = 1MHz OSC = 1Vrms, DC = 50V	Max 50	pF


KU5N12 On-State Voltage - On-State Current



KU5N12 Breakover Voltage - Junction Temperature




KU5N12 Holding Current - Junction Temperature



KU5N12

Junction Capacitance



KU5N12 Junction Capacitance

