






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	SEE DETAIL	"A" +/- .062	"B"	"C"	MARKER ACROSS	TUBING COLOR	SEE STYLE
H200X064FIT	A	2.00 [50.80]	3.50 [88.90]	.75 [19.1]	1	WHITE	A
H100X064FIT	B	1.00 [25.40]		.75 [19.1]	2	WHITE	
H050X064FIT	C	0.50 [12.70]		.75 [19.1]	4	WHITE	
H200X064FIT-B	A	2.00 [50.80]		.75 [19.1]	1	WHITE	B
H100X064FIT-B	B	1.00 [25.40]		.75 [19.1]	2	WHITE	
H050X064FIT-B	C	0.50 [12.70]		.75 [19.1]	4	WHITE	

NOTES:
1. DIMENSION IN [] ARE
IN MILLIMETERS.

CAD FILENAME/LAYERS		I00923NU-DC-C10219/07G	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING H***x064F** OPTIMUM		COMPUTER PRINTABLE HEAT SHRINK MARKERS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .020 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
6	12/2/10	RVU	Change boxes design.
5	5/21/09	RVU	+/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: .64 +/- .062 WAS .640. MAT'L, HSK TUBING GMH531, 3.5 WIDE LINER WAS GMHS. ADD "A" +/- .062. ADD STYLE B VIEW FOR BULK BOX. VIEW UPDATE.
REV	DATE	BY	CHK
DESCRIPTION		ECN - R	CUST SUP
DRAWN BY RVU		MAT'L: HEATSHRINK TUBING GMH531, 3.5 WIDE LINER	
DATE 9-29-04		SCALE NTS	
CHK'D		DRAWING NO. C10219	
		DWG A SIZE	