

Part Number: 48106-1413

2.00mm Pitch, Wire-to-Board, 14 Circuits, Crimp Housing, Blue

Image not available

Status: **OBSOLETE**
 Replacement: Contact Molex
 Series: 48106
 Category: Crimp Housings

Go to Part Detail ▾

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)
[Email this page](#)

Series Image - Reference only

Mates With Part(s):
48107, 48148Use With:
48105

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV: Not Relevant

EU RoHS: Compliant

China RoHS:

REACH SVHC: Contains SVHC (2015 June 15): No

Low-Halogen Status: Low-Halogen

[RoHS Certificate of Compliance \(PDF\)](#)[Multiple Part Product Compliance Form](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Obsolete
Category	Crimp Housings
Series	48106
Application	Signal
Product Name	N/A
UPC	822348539123

▼ Physical

Circuits (maximum)	14
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-25°C to +85°C

▼ Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact: 2.0A

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA: LR19980

UL: E29179

▼ Material Info

▼ Reference - Drawing Numbers

Packaging Specification	PK-48106-001
Product Specification	PS-48107-001, RPS-48107-002, RPS-48107-005
Sales Drawing	SD-48106-001
Test Summary	TS-48107-001

