

DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION

NOTES:

- 1 TO DETERMINE DIMENSIONS TAKE N=NR. OF POS.
FOR EXAMPLE, 10 POS., $N \times 2,54 = 25,4\text{mm}$.
FOR ORDERNR. USE BASIC NR.+NR. OF POS.
FOR EXAMPLE, 2×2 POS. = 216603-2 (SHORTEST VERSION)
 2×65 POS. = 6-216603-5 (LONGEST VERSION)

2 HOUSING MATERIAL, GREEN GLASSFILLED POLYESTER, UL 94V-0
CONTACT MATERIAL, PHOSPHORBRONZE.


3 PLATING: $3,0-5,0\mu\text{m}$ TIN.

4 MATES WITH $0,63$ SQUARE/ROUND MODU POSTS.



5 CONTACT-POINT.

6 RECOMMENDED P.C. BOARD-THICKNESS, $1,6\text{mm}$.


7 PRINTED: BASIC PARTNUMBER, THE WORD "AMP", PRODUCTION DATE
AND A DASHED LINE OVER THE LENGTH OF HOUSING TO
INDICATE CONTACT MATING SIDE.




SECTION B-B/TOP VIEW



SECTION A-A



REAR VIEW



BOTTOM VIEW

RECOMMENDED P.C. BOARD-HOLE LAYOUT				FINISH		MATERIAL	PARTNUMBER
				-	-	-	FOR REFERENCE ONLY WILL NOT BE UPDATED
				-	-	-	© COPYRIGHT 19- BY AMP HOLLAND B.V.
				-	-	-	ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
				-	-	-	COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
				-	-	-	THIS DRAWING IS UNPUBLISHED
H1	EG-00-1730-03	TISZA KISS	ZITZ	14MAY03			RELEASED FOR PUBLICATION DEC, 1991
H	EH-0467-97	JvL	RB	06-05-97			
G	EH-1294-96	RdB	RdB	07-NOV-96			
F	H-8257	LvdH	WRA	17 APR '92			
E	ECN H9408	WRA	WRA	19-12-91			
LTR.	REVISION RECORD	DR.	CHK.	DATE			
DR.:	W.R. ANNOKKEE	CHK.:	R. BROENS	APP.:	E. LEIJTENS	DWG. No.	
DATE:	19-12-91	DATE:	19-12-91	DATE:	19-12-91	C-216603	
						REV. LTR.	
						H1	
						SHEET	
						1 OF 1	
						A2	