







SPECIFICATIONS					
WIRING	INPUT		OUTPUT		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD	
				MAX. AMPS	MAX. KVA
SINGLE PHASE	120	60	0-132	1.75	0.23

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ± DECIMALS .XX Holes .06 ANGLES 1° DRAFT 1-1/2° UNITS IN [mm]				TITLE: SPEC. CONTROL DRAWING VARIABLE AC POWER SOURCE MODEL: L221B				 A COMPONENTS CORPORATION OF AMERICA COMPANY DAYTON, OHIO U.S.A.	
MATERIAL: ALL DIMENSIONS APPLY AFTER PLATING				DRAWN BY S.A. SMITH	DATE 3/4/99	FIRST USED ON SCALE DWG.	CUSTOMER APPROVAL DATE		
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.				CHECKER	DATE	WEIGHT APPROX.	CODE IDENT. NO. 83008	DWG. SIZE D	DWG. NO. 065-1025
				ENGINEER	DATE	SCALE 1=1	SHEET 1 OF 1		