

Flexible RF cable G_04133_D

Description

G: RF cables with PE dielectrics

RG59D/RD59 alternative, 75 Ohm, 2 GHz, 85°C, ø6.7 mm, PVC jacket



Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Copper	Wire	0.58 mm
Dielectric	PE (Polyethylene)		3.64 mm
Outer conductor	Copper	Braid, 92%	4.4 mm
Outer conductor	Copper	Braid, 91 %	5 mm
Jacket	PVC (Polyvinyl chloride)	RAL 9005 - bk	6.7 mm +/- 0.1

Print: HUBER+SUHNER G 04133 D 75 Ohm (production order number)

Electrical Data

Impedance	75 Ω +/- 1.5
Operating Frequency	2 GHz
Capacitance	67 pF/m
Velocity of signal propagation	66 %
Signal delay	5.07 ns/m
Screening effectiveness	≥ 80 dB (up to 1 GHz)
Operating voltage	≤ 3 kV _{rms} (at sea level)
Test voltage	6 kV _{rms} (50 Hz/1 min)

Mechanical Data

Weight		8.1 kg/100 m
Min. bending radius	static	35 mm
		67 mm

Environmental Data

Temperature range	-25 °C ... +85 °C
Installation temperature	-20 °C... +60 °C
Halogen free	No
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
1907/2006/EC (REACH)	compliant

Additional Information

Ordering Information

Order as	G_04133_D
----------	-----------

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Suitable Connectors

Cable group	U18 4 mm / 75 Ohm
-------------	-------------------

Flexible RF cable
G_04133_DMatrix typical Attenuation [formula: $(a \cdot f^{0.5} + b \cdot f)$] and maximum Power CW [formula: $(p/f^{0.5})$]

Coefficients:

a = 0.3308

b = 0.0667

 $f_{\max} = 2$

P at 1GHz = 130

Frequency	Nom. attenuation	Nom. attenuation	Max. CW power
(GHz)	(dB / m)	(dB / ft)	(W)
	sea level 25° C ambient temperature	sea level 25° C ambient temperature	sea level 40° C ambient temperature
0,1	0,11	0,034	411
0,2	0,16	0,049	291
0,3	0,2	0,061	237
0,4	0,24	0,072	206
0,5	0,27	0,081	184
0,6	0,3	0,090	168
0,7	0,32	0,099	155
0,8	0,35	0,106	145
0,9	0,37	0,114	137
1,0	0,4	0,121	130
1,1	0,42	0,128	124
1,2	0,44	0,135	119
1,3	0,46	0,141	114
1,4	0,48	0,148	110
1,5	0,51	0,154	106
1,6	0,53	0,160	103
1,7	0,54	0,166	100
1,8	0,56	0,172	97
1,9	0,58	0,178	94
2,0	0,6	0,183	92