



VHLPX6-10W-3WH/B

1.8 m | 6 ft ValuLine® High Performance Low Profile Antenna, dual-polarized, 10.000–10.700 GHz, UBR100, white antenna, polymer white radome without flash, standard pack—one-piece reflector

Replaced By:

VHLPX6-11W-3WH/A 1.8 m | 6 ft ValuLine® High Performance Low Profile Antenna, dual-polarized, 10.000–10.700 GHz, UBR100, white antenna, flexible woven polymer gray radome without flash, standard pack—one-piece reflector

General Specifications

Antenna Type	VHLPX - ValuLine® High Performance Low Profile Antenna, dual-polarized
Diameter, nominal	1.8 m 6 ft
Packing	Standard pack
Radome Color	White
Radome Material	Polymer
Reflector Construction	One-piece reflector
Antenna Input	UBR100
Antenna Color	White
Antenna Type	VHLPX - ValuLine® High Performance Low Profile Antenna, dual-polarized
Diameter, nominal	1.8 m 6 ft
Flash Included	No
Polarization	Dual

Electrical Specifications

Operating Frequency Band	10.000 – 10.700 GHz
Beamwidth, Horizontal	1.2 °
Beamwidth, Vertical	1.2 °
Cross Polarization Discrimination (XPD)	30 dB
Electrical Compliance	Brazil Anatel Class 2 Canada SRSP 310.5 ETSI 302 217 Class 3 US FCC Part 101A
Front-to-Back Ratio	69 dB
Gain, Low Band	43.0 dBi
Gain, Mid Band	43.1 dBi
Gain, Top Band	43.3 dBi
Operating Frequency Band	10.000 – 10.700 GHz
Radiation Pattern Envelope Reference (RPE)	7098B
Return Loss	17.7 dB
VSWR	1.30

Mechanical Specifications

Product Specifications

COMMSCOPE®

VHLPX6-10W-3WH/B

Fine Azimuth Adjustment	±20°
Fine Elevation Adjustment	±15°
Mounting Pipe Diameter	115 mm 4.5 in
Net Weight	95 kg 209 lb
Side Struts, Included	1 inboard
Side Struts, Optional	1 inboard
Wind Velocity Operational	200 km/h 124 mph
Wind Velocity Survival Rating	200 km/h 124 mph

Wind Forces At Wind Velocity Survival Rating


Axial Force (FA)	7128 N 1602 lbf
Side Force (FS)	3531 N 794 lbf
Twisting Moment (MT)	3197 N•m
Weight with 1/2 in (12 mm) Radial Ice	205 kg 452 lb
Zcg with 1/2 in (12 mm) Radial Ice	450 mm 18 in
Zcg without Ice	425 mm 17 in

Product Specifications

COMMSCOPE®

VHLPX6-10W-3WH/B

Wind Forces At Wind Velocity Survival Rating Image



Packed Dimensions


Gross Weight, Packed Antenna	130.0 kg 286.6 lb
Height	214.0 cm 84.3 in
Length	205.0 cm 80.7 in
Volume	2.9 m ³
Width	66.0 cm 26.0 in

Product Specifications

COMMSCOPE®

VHLPX6-10W-3WH/B

Antenna Dimensions And Mounting Information



Dimensions in Inches (mm)					
Antenna Size, ft (m)	A	B	C	D	E
6	73.6 (1871)	16.3 (415)	38.5 (972)	19.3 (490)	11.6 (295)

Regulatory Compliance/Certifications

Agency
ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Gain, Mid Band

For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

Operating Frequency Band

Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.

Packing

Andrew standard packing is suitable for export. Antennas are shipped as

Product Specifications

COMMSCOPE®

VHLPX6-10W-3WH/B

standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.

Radiation Pattern Envelope Reference (RPE)	Radiation patterns define an antenna's ability to discriminate against unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining an angular accuracy of +/-1° throughout
Return Loss	The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.
Side Force (FS)	Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Twisting Moment (MT)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
VSWR	Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.
Wind Velocity Operational	The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.
Wind Velocity Survival Rating	The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.