



	1	2	3	4	5	6	7																																																																									
A								A																																																																								
B								B																																																																								
C	P.C.B LAYOUT							C																																																																								
	Material																																																																															
	Terminal body (metal housing): Brass(CuZn) Terminal screw: Steel Zinc plating "-" slot type Contacts: Brass Surface of solder tail: Tin plated Insulator (housing): Thermoplastic (UL94V-0), Green																																																																															
D	Electrical							D																																																																								
	Voltage rating: 300VAC Current rating: 20A Solid wire(AWG): 12-30 Stranded wire(AWG): 12-30 Torque(Lb-in): 3.5 Screw: M3 Wire strip length: 6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  US																																																																															
E								E																																																																								
F								F																																																																								
G	RoHS compliant  File No.: E349947 <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td></td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td>Drawn</td><td>29.07.2009</td><td>Dean</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td>Approved</td><td>19.04.2016</td><td>Winnie</td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>②</td><td>Add the UL File No.</td><td></td><td></td><td></td><td></td></tr><tr><td>X. °</td><td>±1°</td><td></td><td></td><td></td><td></td><td>19.04.2016</td><td>Winnie</td></tr><tr><td>X.X°</td><td>±X°</td><td>①</td><td>Drawn</td><td></td><td></td><td>29.07.2009</td><td>Dean</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td></td><td></td><td>Date</td><td>Name</td></tr></table> ASSMANN WSW/ components ASS 3596 CO rev02 ASSMANN WSW-No. A-TB762-VJxxH Drawing-No. Replace Sheet							Scale	1:1						Customer-No.	TOLERANCE								X.	±0.50				Drawn	29.07.2009	Dean	X.X	±0.30				Approved	19.04.2016	Winnie	X.XX	±0.10							DIM	TOL	②	Add the UL File No.					X. °	±1°					19.04.2016	Winnie	X.X°	±X°	①	Drawn			29.07.2009	Dean	Angle	TOL	Id.	Modification			Date	Name	G
Scale	1:1						Customer-No.																																																																									
TOLERANCE																																																																																
X.	±0.50				Drawn	29.07.2009	Dean																																																																									
X.X	±0.30				Approved	19.04.2016	Winnie																																																																									
X.XX	±0.10																																																																															
DIM	TOL	②	Add the UL File No.																																																																													
X. °	±1°					19.04.2016	Winnie																																																																									
X.X°	±X°	①	Drawn			29.07.2009	Dean																																																																									
Angle	TOL	Id.	Modification			Date	Name																																																																									
H								H																																																																								
	1	2	3	4	5	6	7	SVXXXX																																																																								