

CE **UL** **CSA**

L-10 LIFE AT 40°C:
25 000 hours

Technical drawing of a mechanical part, showing a front view and a cross-section view.

Front View Dimensions:

- Overall width: 159 ± 0.5
- Overall height: 165 ± 0.3
- Top flange width: 77.5 ± 0.5
- Top flange thickness: 6.06
- Distance from top flange to center: 91.4 ± 0.5
- Distance from top flange to bottom flange: 104.27 ± 0.3
- Distance from top flange to bottom flange (total): 127.89 ± 0.3
- Distance from left side to center: 6.89
- Distance from center to right side: 24.38 ± 0.3
- Distance from center to right side (total): 144.27 ± 0.3
- Bottom flange thickness: $3 \times \varnothing 4.77$

Cross-section View Dimensions:




- Overall width: 40.1 ± 0.5
- Overall height: 32.6 ± 0.5
- Distance from top flange to center: 66.5 ± 0.5
- Distance from top flange to bottom flange: 300 ± 10
- Distance from top flange to bottom flange (total): 10

Notes:

- Air flow direction is indicated by an arrow pointing left.
- Dimensions are in millimeters.

Electrical protection: impedance protected
Housing material: plastic UL 94 VO
Impeller material: plastic UL 94 VO
Weight: 588 g

- speed sensor
- alarm

[illegible]

See page: 162