

## 16-BIT EDGE-TRIGGERED D-TYPE FLIP-FLOP WITH 3-STATE OUTPUTS

Check for Samples: [SN74AUCH16374](#)


### FEATURES

- Member of the Texas Instruments Widebus™ Family
- Optimized for 1.8-V Operation and Is 3.6-V I/O Tolerant to Support Mixed-Mode Signal Operation
- $I_{off}$  Supports Partial-Power-Down Mode Operation
- Sub-1-V Operable
- Max  $t_{pd}$  of 2.8 ns at 1.8 V
- Low Power Consumption, 20  $\mu$ A Max  $I_{CC}$
- $\pm 8$ -mA Output Drive at 1.8 V
- Bus Hold on Data Inputs Eliminates the Need for External Pullup/Pulldown Resistors
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1000-V Charged-Device Model (C101)

### DESCRIPTION/ORDERING INFORMATION

This 16-bit edge-triggered D-type flip-flop is operational at 0.8-V to 2.7-V  $V_{CC}$ , but is designed specifically for 1.65-V to 1.95-V  $V_{CC}$  operation.

DGG OR DGV PACKAGE  
(TOP VIEW)



The SN74AUCH16374 is particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers. It can be used as two 8-bit flip-flops or one 16-bit flip-flop. On the positive transition of the clock (CLK) input, the Q outputs of the flip-flop take on the logic levels set up at the data (D) inputs.

A buffered output-enable ( $\overline{OE}$ ) input can be used to place the eight outputs in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and increased drive provide the capability to drive bus lines without interface or pullup components.

$\overline{OE}$  does not affect internal operations of the latch. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Widebus is a trademark of Texas Instruments.

**ORDERING INFORMATION**

| <b>T<sub>A</sub></b> | <b>PACKAGE<sup>(1)</sup></b> |               | <b>ORDERABLE PART NUMBER</b> | <b>TOP-SIDE MARKING</b> |
|----------------------|------------------------------|---------------|------------------------------|-------------------------|
| –40°C to 85°C        | TSSOP – DGG                  | Tape and reel | SN74AUCH16374DGGR            | AUCH16374               |
|                      | TVSOP – DGV                  | Tape and reel | SN74AUCH16374DGVR            | MJ374                   |
|                      | VFBGA – GQL                  | Tape and reel | SN74AUCH16374GQLR            | MJ374                   |
|                      | VFBGA – ZQL                  | Tape and reel | SN74AUCH16374ZQLR            | MJ374                   |

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).


**DESCRIPTION/ORDERING INFORMATION(CONTINUED)**

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

Active bus-hold circuitry holds unused or undriven inputs at a valid logic state. Use of pullup or pulldown resistors with the bus-hold circuitry is not recommended.

This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

**GQL or ZQL PACKAGE  
(TOP VIEW)**




**TERMINAL ASSIGNMENTS<sup>(1)</sup>**

|          | 1                 | 2   | 3               | 4               | 5   | 6    |
|----------|-------------------|-----|-----------------|-----------------|-----|------|
| <b>A</b> | 1 $\overline{OE}$ | NC  | NC              | NC              | NC  | 1CLK |
| <b>B</b> | 1Q2               | 1Q1 | GND             | GND             | 1D1 | 1D2  |
| <b>C</b> | 1Q4               | 1Q3 | V <sub>CC</sub> | V <sub>CC</sub> | 1D3 | 1D4  |
| <b>D</b> | 1Q6               | 1Q5 | GND             | GND             | 1D5 | 1D6  |
| <b>E</b> | 1Q8               | 1Q7 |                 |                 | 1D7 | 1D8  |
| <b>F</b> | 2Q1               | 2Q2 |                 |                 | 2D2 | 2D1  |
| <b>G</b> | 2Q3               | 2Q4 | GND             | GND             | 2D4 | 2D3  |
| <b>H</b> | 2Q5               | 2Q6 | V <sub>CC</sub> | V <sub>CC</sub> | 2D6 | 2D5  |
| <b>J</b> | 2Q7               | 2Q8 | GND             | GND             | 2D8 | 2D7  |
| <b>K</b> | 2 $\overline{OE}$ | NC  | NC              | NC              | NC  | 2CLK |

(1) NC - No internal connection

**FUNCTION TABLE  
(EACH FLIP-FLOP)**

| INPUTS          |        |   | OUTPUT<br>Q    |
|-----------------|--------|---|----------------|
| $\overline{OE}$ | CLK    | D |                |
| L               | ↑      | H | H              |
| L               | ↑      | L | L              |
| L               | H or L | X | Q <sub>0</sub> |
| H               | X      | X | Z              |

**LOGIC DIAGRAM (POSITIVE LOGIC)**

Pin numbers shown are for the DGG and DGV packages.

**Absolute Maximum Ratings<sup>(1)</sup>**

over operating free-air temperature range (unless otherwise noted)

|               |   | MIN             | MAX            | UNIT |
|---------------|---|-----------------|----------------|------|
| $V_{CC}$      | Supply voltage range  | -0.5            | 3.6            | V    |
| $V_I$         | Input voltage range <sup>(2)</sup>  | -0.5            | 3.6            | V    |
| $V_O$         | Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup> | -0.5            | 3.6            | V    |
| $V_O$         | Output voltage range <sup>(2)</sup>   | -0.5            | $V_{CC} + 0.5$ | V    |
| $I_{IK}$      | Input clamp current   | $V_I < 0$       | -50            | mA   |
| $I_{OK}$      | Output clamp current  | $V_O < 0$       | -50            | mA   |
| $I_O$         | Continuous output current   |                 | $\pm 20$       | mA   |
|               | Continuous current through each $V_{CC}$ or GND   |                 | $\pm 100$      | mA   |
| $\theta_{JA}$ | Package thermal impedance <sup>(3)</sup>  | DGG package     | 70             | °C/W |
|               |   | DGV package     | 58             |      |
|               |   | ZQL/GQL package | 42             |      |
| $T_{stg}$     | Storage temperature range   | -65             | 150            | °C   |

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) The package thermal impedance is calculated in accordance with JESD 51-7.

**Recommended Operating Conditions<sup>(1)</sup>**

|                     |                                    | MIN                                      | MAX                  | UNIT     |   |
|---------------------|------------------------------------|--|----------------------|----------|---|
| $V_{CC}$            | Supply voltage                     | 0.8                                      | 2.7                  | V        |   |
| $V_{IH}$            | High-level input voltage           | $V_{CC} = 0.8\text{ V}$                  | $V_{CC}$             | V        |   |
|                     |                                    | $V_{CC} = 1.1\text{ V to }1.95\text{ V}$ | $0.65 \times V_{CC}$ |          |   |
|                     |                                    | $V_{CC} = 2.3\text{ V to }2.7\text{ V}$  | 1.7                  |          |   |
| $V_{IL}$            | Low-level input voltage            | $V_{CC} = 0.8\text{ V}$                  | 0                    | V        |   |
|                     |                                    | $V_{CC} = 1.1\text{ V to }1.95\text{ V}$ | $0.35 \times V_{CC}$ |          |   |
|                     |                                    | $V_{CC} = 2.3\text{ V to }2.7\text{ V}$  | 0.7                  |          |   |
| $V_I$               | Input voltage                      | 0  | 3.6                  | V        |   |
| $V_O$               | Output voltage                     | Active state                             | 0                    | $V_{CC}$ | V |
|                     |                                    | 3-state                                  | 0                    | 3.6      | V |
| $I_{OH}$            | High-level output current          | $V_{CC} = 0.8\text{ V}$                  | -0.7                 | mA       |   |
|                     |                                    | $V_{CC} = 1.1\text{ V}$                  | -3                   |          |   |
|                     |                                    | $V_{CC} = 1.4\text{ V}$                  | -5                   |          |   |
|                     |                                    | $V_{CC} = 1.65\text{ V}$                 | -8                   |          |   |
|                     |                                    | $V_{CC} = 2.3\text{ V}$                  | -9                   |          |   |
| $I_{OL}$            | Low-level output current           | $V_{CC} = 0.8\text{ V}$                  | 0.7                  | mA       |   |
|                     |                                    | $V_{CC} = 1.1\text{ V}$                  | 3                    |          |   |
|                     |                                    | $V_{CC} = 1.4\text{ V}$                  | 5                    |          |   |
|                     |                                    | $V_{CC} = 1.65\text{ V}$                 | 8                    |          |   |
|                     |                                    | $V_{CC} = 2.3\text{ V}$                  | 9                    |          |   |
| $\Delta t/\Delta v$ | Input transition rise or fall rate |  | 20                   | ns/V     |   |
| $T_A$               | Operating free-air temperature     | -40                                      | 85                   | °C       |   |

(1) All unused inputs of the device must be held at  $V_{CC}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

## Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER                        |                                       | TEST CONDITIONS   | V <sub>CC</sub> | MIN                   | TYP <sup>(1)</sup> | MAX  | UNIT |
|----------------------------------|---------------------------------------|---|-----------------|-----------------------|--------------------|------|------|
| V <sub>OH</sub>                  |                                       | I <sub>OH</sub> = –100 μA                                   | 0.8 V to 2.7 V  | V <sub>CC</sub> – 0.1 |                    |      | V    |
|                                  |                                       | I <sub>OH</sub> = –0.7 mA                                   | 0.8 V           | 0.55                  |                    |      |      |
|                                  |                                       | I <sub>OH</sub> = –3 mA                                     | 1.1 V           | 0.8                   |                    |      |      |
|                                  |                                       | I <sub>OH</sub> = –5 mA                                     | 1.4 V           | 1                     |                    |      |      |
|                                  |                                       | I <sub>OH</sub> = –8 mA                                     | 1.65 V          | 1.2                   |                    |      |      |
|                                  |                                       | I <sub>OH</sub> = –9 mA                                     | 2.3 V           | 1.8                   |                    |      |      |
| V <sub>OL</sub>                  |                                       | I <sub>OL</sub> = 100 μA                                    | 0.8 V to 2.7 V  |                       |                    | 0.2  | V    |
|                                  |                                       | I <sub>OL</sub> = 0.7 mA                                    | 0.8 V           | 0.25                  |                    |      |      |
|                                  |                                       | I <sub>OL</sub> = 3 mA                                      | 1.1 V           |                       |                    | 0.3  |      |
|                                  |                                       | I <sub>OL</sub> = 5 mA                                      | 1.4 V           |                       |                    | 0.4  |      |
|                                  |                                       | I <sub>OL</sub> = 8 mA                                      | 1.65 V          |                       |                    | 0.45 |      |
|                                  |                                       | I <sub>OL</sub> = 9 mA                                      | 2.3 V           |                       |                    | 0.6  |      |
| I <sub>I</sub>                   | All inputs                            | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 0 to 2.7 V      |                       |                    | ±5   | μA   |
| I <sub>BHL</sub> <sup>(2)</sup>  |                                       | V <sub>I</sub> = 0.35 V                                     | 1.1 V           | 10                    |                    |      | μA   |
|                                  |                                       | V <sub>I</sub> = 0.47 V                                     | 1.4 V           | 15                    |                    |      |      |
|                                  |                                       | V <sub>I</sub> = 0.57 V                                     | 1.65 V          | 20                    |                    |      |      |
|                                  |                                       | V <sub>I</sub> = 0.7 V                                      | 2.3 V           | 40                    |                    |      |      |
| I <sub>BHH</sub> <sup>(3)</sup>  |                                       | V <sub>I</sub> = 0.8 V                                      | 1.1 V           | –5                    |                    |      | μA   |
|                                  |                                       | V <sub>I</sub> = 0.9 V                                      | 1.4 V           | –15                   |                    |      |      |
|                                  |                                       | V <sub>I</sub> = 1.07 V                                     | 1.65 V          | –20                   |                    |      |      |
|                                  |                                       | V <sub>I</sub> = 1.7 V                                      | 2.3 V           | –40                   |                    |      |      |
| I <sub>BHLO</sub> <sup>(4)</sup> | V <sub>I</sub> = 0 to V <sub>CC</sub> |   | 1.3 V           | 75                    |                    |      | μA   |
|                                  |                                       |   | 1.6 V           | 125                   |                    |      |      |
|                                  |                                       |   | 1.95 V          | 175                   |                    |      |      |
|                                  |                                       |   | 2.7 V           | 275                   |                    |      |      |
| I <sub>BHHO</sub> <sup>(5)</sup> | V <sub>I</sub> = 0 to V <sub>CC</sub> |   | 1.3 V           | –75                   |                    |      | μA   |
|                                  |                                       |   | 1.6 V           | –125                  |                    |      |      |
|                                  |                                       |   | 1.95 V          | –175                  |                    |      |      |
|                                  |                                       |   | 2.7 V           | –275                  |                    |      |      |
| I <sub>off</sub>                 |                                       | V <sub>I</sub> or V <sub>O</sub> = 2.7 V                    | 0               |                       |                    | ±10  | μA   |
| I <sub>OZ</sub>                  |                                       | V <sub>O</sub> = V <sub>CC</sub> or GND                     | 2.7 V           |                       |                    | ±10  | μA   |
| I <sub>CC</sub>                  |                                       | V <sub>I</sub> = V <sub>CC</sub> or GND, I <sub>O</sub> = 0 | 0.8 V to 2.7 V  |                       |                    | 20   | μA   |
| C <sub>i</sub>                   |                                       | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 2.5 V           | 3                     |                    |      | pF   |
| C <sub>o</sub>                   |                                       | V <sub>O</sub> = V <sub>CC</sub> or GND                     | 2.5 V           | 5                     |                    |      | pF   |

(1) All typical values are at T<sub>A</sub> = 25°C.

(2) The bus-hold circuit can sink at least the minimum low sustaining current at V<sub>IL</sub> max. I<sub>BHL</sub> should be measured after lowering V<sub>IN</sub> to GND and then raising it to V<sub>IL</sub> max.

(3) The bus-hold circuit can source at least the minimum high sustaining current at V<sub>IH</sub> min. I<sub>BHH</sub> should be measured after raising V<sub>IN</sub> to V<sub>CC</sub> and then lowering it to V<sub>IH</sub> min.

(4) An external driver must source at least I<sub>BHLO</sub> to switch this node from low to high.

(5) An external driver must sink at least I<sub>BHHO</sub> to switch this node from high to low.

## Timing Requirements

over recommended operating free-air temperature range (unless otherwise noted) (see [Figure 1](#))

|                    |                                 | V <sub>CC</sub> = 0.8 V | V <sub>CC</sub> = 1.2 V<br>± 0.1 V |     | V <sub>CC</sub> = 1.5 V<br>± 0.1 V |     | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |     | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     | UNIT |
|--------------------|---------------------------------|-------------------------|------------------------------------|-----|------------------------------------|-----|-------------------------------------|-----|------------------------------------|-----|------|
|                    |                                 | TYP                     | MIN                                | MAX | MIN                                | MAX | MIN                                 | MAX | MIN                                | MAX |      |
| f <sub>clock</sub> | Clock frequency                 | 85                      | 250                                |     | 250                                |     | 250                                 |     | 250                                |     | MHz  |
| t <sub>w</sub>     | Pulse duration, CLK high or low | 5.9                     | 1.9                                |     | 1.9                                |     | 1.9                                 |     | 1.9                                |     | ns   |
| t <sub>su</sub>    | Setup time, data before CLK↑    | 1.4                     | 1.2                                |     | 0.7                                |     | 0.6                                 |     | 0.6                                |     | ns   |
| t <sub>h</sub>     | Hold time, data after CLK↑      | 0.1                     | 0.4                                |     | 0.4                                |     | 0.4                                 |     | 0.4                                |     | ns   |

## Switching Characteristics

over recommended operating free-air temperature range (unless otherwise noted) (see [Figure 1](#))

| PARAMETER        | FROM<br>(INPUT) | TO<br>(OUTPUT) | V <sub>CC</sub> = 0.8 V | V <sub>CC</sub> = 1.2 V<br>± 0.1 V |     | V <sub>CC</sub> = 1.5 V<br>± 0.1 V |     | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |     |     | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     | UNIT |
|------------------|-----------------|----------------|-------------------------|------------------------------------|-----|------------------------------------|-----|-------------------------------------|-----|-----|------------------------------------|-----|------|
|                  |                 |                | TYP                     | MIN                                | MAX | MIN                                | MAX | MIN                                 | TYP | MAX | MIN                                | MAX |      |
| f <sub>max</sub> |                 |                | 85                      | 250                                |     | 250                                |     | 250                                 |     |     | 250                                |     | MHz  |
| t <sub>pd</sub>  | CLK             | Q              | 7.3                     | 1                                  | 4.5 | 0.8                                | 2.9 | 0.7                                 | 1.5 | 2.8 | 0.7                                | 2.2 | ns   |
| t <sub>en</sub>  | $\overline{OE}$ | Q              | 7                       | 1.2                                | 5.3 | 0.8                                | 3.6 | 0.8                                 | 1.5 | 2.9 | 0.7                                | 2.2 | ns   |
| t <sub>dis</sub> | $\overline{OE}$ | Q              | 8.2                     | 2                                  | 7.1 | 1                                  | 4.8 | 1.4                                 | 2.7 | 4.5 | 0.5                                | 2.2 | ns   |


## Operating Characteristics<sup>(1)</sup>

T<sub>A</sub> = 25°C

| PARAMETER  |                                     |   | TEST<br>CONDITIONS   | V <sub>CC</sub> = 0.8 V | V <sub>CC</sub> = 1.2 V | V <sub>CC</sub> = 1.5 V | V <sub>CC</sub> = 1.8 V | V <sub>CC</sub> = 2.5 V | UNIT |
|--|-------------------------------------|---|--|-------------------------|-------------------------|-------------------------|-------------------------|-------------------------|------|
|  |                                     |   |  | TYP                     | TYP                     | TYP                     | TYP                     | TYP                     |      |
| C <sub>pd</sub> <sup>(2)</sup><br>(each<br>output) | Power<br>dissipation<br>capacitance | Outputs<br>enabled,<br>1 output<br>switching                  | 1 f <sub>data</sub> = 5 MHz,<br>1 f <sub>clk</sub> = 10 MHz,<br>1 f <sub>out</sub> = 5 MHz,<br>$\overline{OE}$ = GND,<br>C <sub>L</sub> = 0 pF                       | 24                      | 24                      | 24.1                    | 26.2                    | 31.2                    | pF   |
| C <sub>pd</sub><br>(Z)                             | Power<br>dissipation<br>capacitance | Outputs<br>disabled,<br>1 clock<br>and 1<br>data<br>switching | 1 f <sub>data</sub> = 5 MHz,<br>1 f <sub>clk</sub> = 10 MHz,<br>f <sub>out</sub> = not<br>switching,<br>$\overline{OE}$ = V <sub>CC</sub> ,<br>C <sub>L</sub> = 0 pF | 7.5                     | 7.5                     | 8                       | 9.4                     | 13.2                    | pF   |
| C <sub>pd</sub> <sup>(3)</sup><br>(each<br>clock)  | Power<br>dissipation<br>capacitance | Outputs<br>disabled,<br>clock<br>only<br>switching            | 1 f <sub>data</sub> = 0 MHz,<br>1 f <sub>clk</sub> = 10 MHz,<br>f <sub>out</sub> = not<br>switching,<br>$\overline{OE}$ = V <sub>CC</sub> ,<br>C <sub>L</sub> = 0 pF | 13.8                    | 13.8                    | 14                      | 14.7                    | 17.5                    | pF   |





- (1) Total device C<sub>pd</sub> for multiple (n) outputs switching and (y) clocks inputs switching = {n \* C<sub>pd</sub> (each output)} + {y \* C<sub>pd</sub> (each clock)}.
- (2) C<sub>pd</sub> (each output) is the C<sub>pd</sub> for each data bit (input and output circuitry) as it operates at 5 MHz (Note: the clock is operating at 10 MHz in this test, but its I<sub>CC</sub> component has been subtracted out).
- (3) C<sub>pd</sub> (each clock) is the C<sub>pd</sub> for the clock circuitry only as it operates at 10 MHz.

PARAMETER MEASUREMENT INFORMATION



| TEST              | S1                |
|-------------------|-------------------|
| $t_{PLH}/t_{PHL}$ | Open              |
| $t_{PLZ}/t_{PZL}$ | $2 \times V_{CC}$ |
| $t_{PHZ}/t_{PZH}$ | GND               |

| $V_{CC}$           | $C_L$ | $R_L$        | $V_{\Delta}$ |
|--------------------|-------|--------------|--------------|
| 0.8 V              | 15 pF | 2 k $\Omega$ | 0.1 V        |
| 1.2 V $\pm$ 0.1 V  | 15 pF | 2 k $\Omega$ | 0.1 V        |
| 1.5 V $\pm$ 0.1 V  | 15 pF | 2 k $\Omega$ | 0.1 V        |
| 1.8 V $\pm$ 0.15 V | 30 pF | 1 k $\Omega$ | 0.15 V       |
| 2.5 V $\pm$ 0.2 V  | 30 pF | 500 $\Omega$ | 0.15 V       |



- NOTES: A.  $C_L$  includes probe and jig capacitance.  
 B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.  
 C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O = 50 \Omega$ , slew rate  $\geq$  1 V/ns.  
 D. The outputs are measured one at a time, with one transition per measurement.  
 E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .  
 F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .  
 G.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .  
 H. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms

---

**Changes from Revision D (May 2005) to Revision E****Page**

- 
- Added new ZQL package to the datasheet. .... [2](#)
-

**PACKAGING INFORMATION**

| Orderable Device  | Status<br>(1) | Package Type               | Package Drawing | Pins | Package Qty | Eco Plan<br>(2)         | Lead/Ball Finish | MSL Peak Temp<br>(3) | Samples<br>(Requires Login) |
|-------------------|---------------|----------------------------|-----------------|------|-------------|-------------------------|------------------|----------------------|-----------------------------|
| 74AUCH16374DGGRE4 | ACTIVE        | TSSOP                      | DGG             | 48   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   |                             |
| 74AUCH16374DGGRG4 | ACTIVE        | TSSOP                      | DGG             | 48   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   |                             |
| 74AUCH16374DGVRE4 | ACTIVE        | TVSOP                      | DGV             | 48   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   |                             |
| 74AUCH16374DGVRG4 | ACTIVE        | TVSOP                      | DGV             | 48   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   |                             |
| SN74AUCH16374DGGR | ACTIVE        | TSSOP                      | DGG             | 48   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   |                             |
| SN74AUCH16374DGVR | ACTIVE        | TVSOP                      | DGV             | 48   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   |                             |
| SN74AUCH16374GQLR | OBSOLETE      | BGA<br>MICROSTAR<br>JUNIOR | GQL             | 56   |             | TBD                     | Call TI          | Call TI              |                             |
| SN74AUCH16374ZQLR | ACTIVE        | BGA<br>MICROSTAR<br>JUNIOR | ZQL             | 56   | 1000        | Green (RoHS & no Sb/Br) | SNAGCU           | Level-1-260C-UNLIM   |                             |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION




### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



\*All dimensions are nominal

| Device            | Package Type         | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|----------------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AUCH16374DGGR | TSSOP                | DGG             | 48   | 2000 | 330.0              | 24.4               | 8.6     | 15.8    | 1.8     | 12.0    | 24.0   | Q1            |
| SN74AUCH16374DGVR | TVSOP                | DGV             | 48   | 2000 | 330.0              | 16.4               | 7.1     | 10.2    | 1.6     | 12.0    | 16.0   | Q1            |
| SN74AUCH16374ZQLR | BGA MICROSTAR JUNIOR | ZQL             | 56   | 1000 | 330.0              | 16.4               | 4.8     | 7.3     | 1.5     | 8.0     | 16.0   | Q1            |


**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device            | Package Type         | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|----------------------|-----------------|------|------|-------------|------------|-------------|
| SN74AUCH16374DGGR | TSSOP                | DGG             | 48   | 2000 | 367.0       | 367.0      | 45.0        |
| SN74AUCH16374DGVR | TVSOP                | DGV             | 48   | 2000 | 367.0       | 367.0      | 38.0        |
| SN74AUCH16374ZQLR | BGA MICROSTAR JUNIOR | ZQL             | 56   | 1000 | 333.2       | 345.9      | 28.6        |

ZQL (R-PBGA-N56)

PLASTIC BALL GRID ARRAY




- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MO-285 variation BA-2.
  - D. This package is Pb-free. Refer to the 56 GQL package (drawing 4200583) for tin-lead (SnPb).

DGV (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE


24 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.  
 D. Falls within JEDEC: 24/48 Pins – MO-153  
 14/16/20/56 Pins – MO-194

GQL (R-PBGA-N56)

PLASTIC BALL GRID ARRAY




- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MO-285 variation BA-2.
  - D. This package is tin-lead (SnPb). Refer to the 56 ZQL package (drawing 4204437) for lead-free.

DGG (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-153

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

|                              |  |
|------------------------------|--|
| Audio                        | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                               |
| Amplifiers                   | <a href="http://amplifier.ti.com">amplifier.ti.com</a>                               |
| Data Converters              | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>                       |
| DLP® Products                | <a href="http://www.dlp.com">www.dlp.com</a>   |
| DSP                          | <a href="http://dsp.ti.com">dsp.ti.com</a>   |
| Clocks and Timers            | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>                             |
| Interface                    | <a href="http://interface.ti.com">interface.ti.com</a>                               |
| Logic                        | <a href="http://logic.ti.com">logic.ti.com</a>                                       |
| Power Mgmt                   | <a href="http://power.ti.com">power.ti.com</a>                                       |
| Microcontrollers             | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a>                   |
| RFID                         | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>                                 |
| OMAP Applications Processors | <a href="http://www.ti.com/omap">www.ti.com/omap</a>                                 |
| Wireless Connectivity        | <a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a> |

### Applications

|                               |  |
|-------------------------------|--|
| Automotive and Transportation | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)