

REVISION AX

NOTES:

1. $\varnothing$ REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM CONTACT PUSHOUT FORCE: 0.5 LB.
3. MAXIMUM ALLOWABLE BOW .003[0.08] IN/IN AFTER ASSEMBLY.
4. FOR A 1 POSITION SINGLE ROW ALL SPACERS ARE TO BE LBS-S.
5. SPACERS SHALL BE ASSEMBLED AS SHOWN WITH SNAP GROOVES AWAY FROM SSW BODY.
6. SINGLE ROW, 33 POS PART TO USE 31 POS AND 2 POS SPACERS.

DO NOT
SCALE FROM
THIS PRINT




FIG 1
ESW-1XX-XX-X-S SHOWN

ESW-1XX-XX-X-X-XX-XX

CONTACT STYLE
SOLDER TAIL
STANDARD INSERTION USE C-8-X-X
LOW INSERTION USE C-17-X-X
(SEE TABLE 1)

BODY LENGTH SPEC
POSITIONS 01 THRU 36 (SEE FIG 1)
(SEE NOTE 4 FOR ONE POSITION
SINGLE ROW)
(FOR 33 POS, SEE NOTE 6)

LEAD STYLE SPECIFICATION
(SEE TABLE 1)

POLARIZING OPTION
INDICATES POS
(SEE FIG 3, SHT 2)

LOCKING LEAD OPTION
-LL (SEE FIG 4, SHT 2)
(N/A ON 1 OR 2
POSITION SINGLE ROW)

ROW SPECIFICATION
-S: SINGLE (USE SSW-50-S)
-D: DOUBLE (USE SSW-50-D)

PLATING SPECIFICATION

- G: 20μ" SELECTIVE GOLD IN CONTACT AREA, 3μ" SELECTIVE GOLD ON TAIL.
- T: MATTE TIN ON ENTIRE PIN.
- (STANDARD INSERTION FORCE ONLY)
- S: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
- H: 30μ" SELECTIVE GOLD IN CONTACT AREA, 3μ" SELECTIVE GOLD ON TAIL.
- F: 3μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
- E: 50μ" SELECTIVE GOLD IN CONTACT AREA, 3μ" SELECTIVE GOLD ON TAIL.
- L: 10μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.




FIG 2
ESW-1XX-XX-X-D SHOWN




TABLE 1						
STANDARD INSERTION FORCE	CONTACT	SPACER SPECIFICATION (SEE NOTE 4)		"B"	"C"	"D"
		ESW-S	ESW-D			
-12	C-8-2-X			.090 [2.29]	.435 [11.05]	.525 [13.34]
-13	C-8-3-X			.290 [7.37]	.435 [11.05]	.725 [18.42]
-14	C-8-5-X			.480 [12.19]	.435 [11.05]	.915 [23.24]
-23	C-8-3-X	(1) SUB-SSB-32	(1) DSB-XX	.190 [4.83]	.535 [13.59]	.725 [18.42]
-24	C-8-5-X	(1) SUB-SSB-32	(1) DSB-XX	.380 [9.65]	.535 [13.59]	.915 [23.24]
-33	C-8-3-X	(2) SUB-SSB-32	(2) DSB-XX	.090 [2.29]	.635 [16.13]	.725 [18.42]
-34	C-8-5-X	(2) SUB-SSB-32	(2) DSB-XX	.280 [7.11]	.635 [16.13]	.915 [23.24]
-44	C-8-5-X	(1) ESS-XX-S	(3) DSB-XX	.180 [4.57]	.735 [18.67]	.915 [23.24]
LOW INSERTION FORCE						
-37	C-17-2-X			.090 [2.29]	.435 [11.05]	.525 [13.34]
-38	C-17-3-X			.290 [7.37]	.435 [11.05]	.725 [18.42]
-39	C-17-5-X			.480 [12.19]	.435 [11.05]	.915 [23.24]
-48	C-17-3-X	(1) SUB-SSB-32	(1) DSB-XX	.190 [4.83]	.535 [13.59]	.725 [18.42]
-49	C-17-5-X	(1) SUB-SSB-32	(1) DSB-XX	.380 [9.65]	.535 [13.59]	.915 [23.24]
-58	C-17-3-X	(2) SUB-SSB-32	(2) DSB-XX	.090 [2.29]	.635 [16.13]	.725 [18.42]
-59	C-17-5-X	(2) SUB-SSB-32	(2) DSB-XX	.280 [7.11]	.635 [16.13]	.915 [23.24]
-69	C-17-5-X	(1) ESS-XX-S	(3) DSB-XX	.180 [4.57]	.735 [18.67]	.915 [23.24]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1
SSW: LCP, UL 94 V0, COLOR: BLACK
SSB, ESS, DSB: PBT, UL 94 V0, COLOR: BLACK
LBS: HTN, UL 94 V0, COLOR: BLACK
CONTACT: PHOS BRONZE

F:\DWG\MISC\MKTG\ESW-1XX-XX-X-X-XX-MKT.SLDDRW

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
ESW STRIP ASM.

DWG. NO.
ESW-1XX-XX-X-X-XX-XX

BY: JORDAN 07/16/1985 SHEET 1 OF 2




FIG 3
POLARIZATION LOCATION
INSERT PK-06-N INTO SPECIFIED POS AND BREAK OFF TAB
(ESW-1XX-XX-X-X-02 SHOWN)
(SAME AS FIG 1, DIFFERENT AS SHOWN)




FIG 4
LOCKING LEAD OPTION
LOCATED ON OR ABOUT THE CENTERLINE
(N/A IN 1 OR 2 POSITION SINGLE ROW)




FIG 5
IN PROCESS 'A'
(LEAD STYLES -13, -14, -23, -24, -33, -34, -44, -38, -39, -48, -49, -58, -59, -69)





FIG 7
TUBE VIEWS

NOTE:
FOR -12 & -37 LEAD STYLES, TUBE PACKAGE -05 THRU -36 POSITIONS ONLY
FOR -13, -23, -33, -38, -48 & -58 LEAD STYLES, TUBE PACKAGE -08 THRU -36 POSITIONS ONLY.
FOR -14, -24, -34, -39, -44, -49, -59, & -69 LEAD STYLES TUBE PACKAGE -05 THRU -36 POSITIONS ONLY.



STEP 1
STEPS:
1. MACHINE FILL SSW-50-D TO 36 POS.
2. MOUNT ESW-36-D.
3. ROTO CUT TO POS. (SEE FIG 1)




FIG 6
IN PROCESS 'B'
(LEAD STYLES -12 & -37)

TABLE 2			
LEAD STYLE	ROW	TUBE	PLUG
-12, -37	-S	PT-1-24-01-46	TP-24
-13, -14, -23, -24, -33, -34, -44, -38, -39, -48, -49, -58, -59, -69		PT-1-24-01-47	TP-09
-12, -37		PT-1-24-03-44	TP-03
-13, -14, -23, -24, -33, -34, -44, -38, -39, -48, -49, -58, -59, -69	-D	PT-1-24-02-47	TP-03

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
ESW STRIP ASM.
DWG. NO.
ESW-1XX-XX-X-X-XX-XX
BY: JORDAN 07/16/1985 SHEET 2 OF 2