

Configurable High Performance SMD TCXO/VCTCXO

ASGTX



ESD Sensitive



RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

➤ OVERVIEW:

ASGTX temperature compensated Crystal Oscillators are designed to accommodate a broad breadth of Precision TCXO requirements, without NRE and extended lead-times. This oscillator series is designed and manufactured by Abracon Corporation and is available to order from 1pc to high volume production quantities.

- **1-5 day quick-turn availability of a TCXO/VCTCXO with LVC MOS output, Any frequency between 10MHz & 250MHz**

For example, if a reference oscillator requirement calls out 49.7521MHz; ± 1.00 ppm TCXO/VCTCXO with **LVC MOS** output, ASGTX can be configured and shipped within 1-5 days and in most cases, same day if order is received before noon. Customers with low-to-mid annual volume requirements find it difficult to procure custom frequency TCXO/VCTCXO's without costly NRE charges and/or long lead-times (≥ 12 weeks).

- **1-5 day quick turn availability of a TCXO/VCTCXO requiring LVDS or LVPECL Differential output, Any frequency between 10MHz to 1.50GHz**

ASGTX is available with either **LVDS** or **LVPECL** output, from **10MHz to 1.50GHz**; at any desired frequency, such as 149.875MHz, 1.00GHz, 1.5GHz, etc. with as tight as ± 1.00 ppm stability over temperature. No other solution in the marketplace currently offers such capability, especially in a small form-factor of 9.0x7.0x2.24 mm.

ASGTX is suitable for a wide variety of precision timing applications where TCXO/VCTCXO's are typically employed. In addition, for high frequency LO requirements, traditionally customers have relied on SAW based oscillators. Such devices are only available at a few fixed frequencies, such as 915MHz, 1.0GHz, etc. They are typically in 9x14mm or bigger packages and vary as much as ± 100 ppm over temperature.

Although ASGTX series will be slightly less favorable in phase noise performance compared to SAW based oscillators, it offers the following key advantages:

- o ± 1.00 ppm stability over -30°C to $+70^{\circ}\text{C}$ & ± 2.00 ppm stability over -40°C to $+85^{\circ}\text{C}$
- o **Any carrier frequency** between 10MHz & 1.50GHz
- o LVC MOS Output (10MHz to 250MHz) **or** LVDS / LVPECL Output (10MHz to 1.50GHz)
- o Small form-factor of 9.0x7.0x2.24 mm
- o No NRE or lead-time

➤ FEATURES:

- 10MHz to 1.50GHz, any Carrier Frequency in differential mode (LVDS or LVPECL)
- 10MHz to 250MHz, any Carrier Frequency in LVC MOS mode
- -40°C to $+85^{\circ}\text{C}$ operating temperature range
- ± 1.0 ppm stability over -30°C to $+70^{\circ}\text{C}$ and ± 2.0 ppm stability over -40°C to $+85^{\circ}\text{C}$
- Minimum guaranteed pull ability of ± 10 ppm in VCTCXO mode
- Good Phase Noise, excellent Harmonics and Spurious content
- Guaranteed rms jitter of 1.80ps maximum @ 1.50GHz carrier
- Immediate availability, 5-day maximum lead-time for small quantities

➤ APPLICATIONS:

- 40G & 100G Ethernet
- WiMax,
- LTE, BTS
- CATV, LAN, LMDS
- Point-to-Point communication networks

Configurable High Performance SMD TCXO/VCTCXO

ASGTX



RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

► KEY ELECTRICAL SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency:	LVC MOS	10		250	MHz	
	LVDS	10		1500		
	LVPECL	10		1500		
Operating Temperature:		-40		+85	°C	
Storage Temperature:		-40		+85	°C	
Frequency Stability:						
Initial Set Tolerance		-1.50	$\leq \pm 1.00$	+1.50	ppm	1 hour after reflow
Stability over operating temperature*	-30°C to +70°C	-1.00		+1.00	ppm	Option “1”
	-40°C to +85°C **	-2.00		+2.00		Option “2”
Aging @ 25°C after one year		-1.00		+1.00	ppm	
Supply Voltage (Vdd):		3.135	3.300	3.465	V	
Startup Time:				3	ms	
Control Voltage:		0	1.55	Vdd	V	In VCTCXO Mode
Frequency Pull:		± 10			ppm	
Phase jitter RMS [t_{jitter}] (12kHz to 20MHz)			<1.00	1.80	ps	

Notes

* Relative to measured frequency post reflow

** Please contact Abracon for ± 1.00 ppm frequency stability over -40°C to +85°C

Key Electrical Specifications – LVC MOS

Parameters		Minimum	Typical	Maximum	Units	Notes
Supply Current (I _{dd}):				45	mA	Frequency dependent
Output Load:				15	pF	
Output Logic Level:	V _{OH}	0.9*V _{dd}			V	
	V _{OL}			0.1*V _{dd}	V	
Rise Time (T _r):				1000	ps	
Fall Time (T _f):				1000	ps	
Duty Cycle:		45		55	%	@1/2Vdd

Configurable High Performance SMD TCXO/VCTCXO

ASGTX



RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

Key Electrical Specifications – LVPECL


Parameters	Minimum	Typical	Maximum	Units	Notes
Supply Current (I _{dd})			60	mA	With typical LVPECL output termination
Output Logic Level	V _{OH}	V _{dd} -1.03		V	
	V _{OL}	V _{dd} -1.85	V _{dd} -1.60	V	
Rise Time (Tr):			350	ps	
Fall Time (Tf):			350	ps	
Differential Duty Cycle:	45		55	%	DODC _{LVPECL}

Key Electrical Specifications – LVDS

Parameters	Minimum	Typical	Maximum	Units	Notes
Supply Current (I _{dd})			40	mA	With typical LVDS output termination
Differential Output Voltage (V _{OD})	175	350		mV	
V _{OD} Magnitude Change (ΔV _{OD})			50	mV	
Offset Voltage (V _{OS})		1.25		V	
V _{OS} Magnitude Change (ΔV _{OS})			50	mV	
Rise Time (Tr):			350	ps	
Fall Time (Tf):			450	ps	
Differential Duty Cycle:	45		55	%	ODC _{LVDS}

OPTIONS & PART IDENTIFICATION:

ASGTX- - MHz - -



Output Type
C = LVCMOS
P = LVPECL
D = LVDS

Frequency in MHz
Please specify the Frequency in MHz e.g. 100.000 MHz

Freq. Stability
1 = ±1ppm over -30 to +70°C
2 = ±2ppm over -40 to +85°C

Packaging
Blank = Bulk (Qty < 250pcs)
T = 1000pcs/Reel
T2 = 250pcs/Reel

C = LVCMOS	Any Carrier Frequency between 10MHz minimum to 250MHz maximum
P = LVPECL	Any Carrier Frequency between 10MHz minimum to 1.50GHz maximum
D = LVDS	Any Carrier Frequency between 10MHz minimum to 1.50GHz maximum

Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

► TYPICAL PHASE NOISE & JITTER CHARACTERISTICS


With LVCMOS Output; 10MHz Carrier




With LVDS Output; 10MHz Carrier



With LVCMOS Output; 25MHz Carrier



With LVDS Output; 25MHz Carrier




Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

► TYPICAL PHASE NOISE & JITTER CHARACTERISTICS


With LVCMS Output; 50MHz Carrier




With LVDS Output; 50MHz Carrier



With LVCMS Output; 120MHz Carrier



With LVPECL Output; 500MHz Carrier




Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

► TYPICAL PHASE NOISE & JITTER CHARACTERISTICS


With LVDS Output; 1.00GHz Carrier



With LVDS Output; 1.2890625GHz Carrier



With LVDS Output; 1.50GHz Carrier




Carrier	RF Output	rms Phase Jitter	Integration Bandwidth
10.00MHz	LVDS	992 fs	12kHz to 5MHz
25.00MHz	LVDS	774 fs	12kHz to 5MHz
50.00MHz	LVDS	768 fs	12kHz to 10MHz
120.00MHz	LVCMS	1.1 ps	12kHz to 20MHz
500.00MHz	LVPECL	956 fs	12kHz to 20MHz
1.00GHz	LVDS	911 fs	12kHz to 20MHz
1.2890625GHz	LVDS	1.03 ps	12kHz to 20MHz
1.50GHz	LVDS	1.55 ps	12kHz to 20MHz




9.0 x 7.0 x 2.24 mm

▷ FREQUENCY STABILITY VS. TEMPERATURE



▷ FREQUENCY PULL VS. CONTROL VOLTAGE (VCTCXO MODE)



Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

OUTLINE DIMENSION:

LVCMOS output




Pin #	Pin Description	
	TCXO	VCTCXO
1	N/C ⁽¹⁾	
2	By-Pass ⁽²⁾	Vc ⁽³⁾
3	GND	
4	RF Output	
5	N/C ⁽¹⁾	
6	Vdd	


N/C ⁽¹⁾ = Please leave these pins electrically floating on the end-PCB

By-Pass ⁽²⁾ = In TCXO configuration, it is recommended that a 1,000pF COG by-pass capacitor is connected between Pin#2 and GND

Vc ⁽³⁾ = Please connect external voltage to pull the oscillator frequency



Recommended Land Pattern



Dimensions: inches [mm]

Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant



9.0 x 7.0 x 2.24 mm

LVDS/LVPECL output




Pin #	Pin Description	
	TCXO	VCTCXO
1	N/C ⁽¹⁾	
2	By-Pass ⁽²⁾	Vc ⁽³⁾
3	GND	
4	RF Output	
5	Complimentary RF Output	
6	Vdd	


N/C ⁽¹⁾ = Please leave this pin electrically floating on the end-PCB

By-Pass ⁽²⁾ = In TCXO configuration, it is recommended that a 1,000pF COG by-pass capacitor is connected between Pin#2 and GND

Vc ⁽³⁾ = Please connect external voltage to pull the oscillator frequency



Recommended Land Pattern




Dimensions: inches [mm]

Configurable High Performance SMD TCXO/VCTCXO

ASGTX




RoHS/RoHS II Compliant




9.0 x 7.0 x 2.24 mm

REFLOW PROFILE:



TAPE & REEL:

Packaging: 1000pcs/reel



Dimensions: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.