



MFA



MFA-PA



Dia. of Lead wire

0-14A $\phi 0.8 \pm 0.05$
15A-19A $\phi 1.0 \pm 0.05$
20A-30A $\phi 1.2 \pm 0.05$


Test Specification according to Standard UL 248-1,14

From:0.1A~10A 125V/250V Approvals:


From:12A~25A 32V Approvals:

From:30A 32V Approvals:

MFA-P



MFA-PR



Rated Current	Breaking capacity	Rated Voltage
100mA	@125V/AC 10KA @250V/AC 35A	125V/250V
125mA		125V/250V
180mA		125V/250V
200mA		125V/250V
250mA		125V/250V
300mA		125V/250V
315mA		125V/250V
400mA		125V/250V
500mA		125V/250V
600mA		125V/250V
830mA		125V/250V
700mA	@125V/AC 10KA @250V/AC 100A	125V/250V
800mA		125V/250V
1A		125V/250V
1.25A		125V/250V
1.5A		125V/250V
1.8A		125V/250V
2A		125V/250V
2.5A		125V/250V
3A		125V/250V
3.15A		125V/250V
3.5A	@125V/AC 10KA @250V/AC 200A	125V/250V
4A		125V/250V
5A		125V/250V
6A		125V/250V
8.3A		125V/250V
7A		125V/250V
8A		125V/250V
10A		125V/250V
12A	@32V/AC 1000A	32V
13A		32V
15A		32V
16A		32V
20A		32V
25A		32V
30A		32V

Electrical Characteristic

Rated Current	1.0 In	1.35 In	2 In
In	Min.	Max.	Max.
0.1A-30A	4 h	3600 S	120 S

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MM
TOLERANCE
DECIMALS ANGULAR
X ± 0.5 $\pm 2^\circ$
XX ± 0.25
DO NOT SCALE DRAWING



P/N:

REV

1.5

CUSTOMER NO.

DRAWN BY LING

CHECKED BY

APPROVED BY

DATE 2007.07.16

SCALE

TITLE

Miniature Cartridge Fuse 6.35x32mm

PART NO. MFA MFA-P MFA-PA MFA-PR

DRAWING NO. AA05062109