

**40V COMPLEMENTARY PAIR ENHANCEMENT MODE MOSFET**
**Product Summary**

Device	V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> Max T <sub>A</sub> = +25°C (Notes 6 & 8)
Q1	40V	45mΩ @ V <sub>GS</sub> = 10V	5.5A
		60mΩ @ V <sub>GS</sub> = 4.5V	4.2A
Q2	-40V	45mΩ @ V <sub>GS</sub> = -10V	-5.8A
		60mΩ @ V <sub>GS</sub> = -4.5V	-4.2A

**Description**

This MOSFET is designed to ensure that R<sub>DS(ON)</sub> of N and P channel FET are matched to minimize losses in both arms of the bridge. The DMC4040SSD is optimized for use in 3-phase brushless DC motor circuits (BLDC), and CCFL backlighting.

**Applications**


- 3-Phase BLDC Motor
- CCFL Backlighting

**Features and Benefits**


- Matched N & P R<sub>DS(ON)</sub> – Minimizes Power Losses
- Fast Switching – Minimizes Switching Losses
- Dual Device – Reduces PCB Area
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**

**Mechanical Data**


- Case: SO-8
- Case Material: Molded Plastic, "Green" Molding Compound.  
UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – Matte Tin Annealed over Copper Leadframe.  
Solderable per MIL-STD-202, Method 208 (E3)
- Weight: 0.074 grams (Approximate)



Top View



Top View




Equivalent Circuit

**Ordering Information** (Note 4)

Product	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
DMC4050SSD-13	C4050SD	13	12	2,500

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
  2. See [http://www.diodes.com/quality/lead\\_free.html](http://www.diodes.com/quality/lead_free.html) for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
  4. For packaging details, go to our website at <http://www.diodes.com/products/packages.html>.

## Marking Information



DII = Manufacturer's Marking  
 C4050SD = Product Type Marking Code  
 YYWW = Date Code Marking  
 YY or YY = Year (ex: 10 = 2010)  
 WW = Week (01 - 53)

## Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)






Characteristic			Symbol	N-Channel - Q1	P-Channel - Q2	Units
Drain-Source Voltage			V <sub>DSS</sub>	40	-40	V
Gate-Source Voltage			V <sub>GSS</sub>	±20	±20	
Continuous Drain Current	V <sub>GS</sub> = 10V	(Notes 6 & 8)	I <sub>D</sub>	5.8	-5.8	A
		T <sub>A</sub> = +70°C (Notes 6 & 8)		4.38	-4.52	
		(Notes 5 & 8)		4.2	-4.2	
		(Notes 5 & 9)		5.3	-5.3	
Pulsed Drain Current	V <sub>GS</sub> = 10V	(Notes 7 & 8)	I <sub>DM</sub>	24.1	-24.9	
Continuous Source Current (Body Diode)			I <sub>S</sub>	2.5	-2.5	
Pulsed Source Current (Body Diode)			I <sub>SM</sub>	24.1	-24.9	

## Thermal Characteristics

Characteristic		Symbol	N-Channel - Q1	P-Channel - Q2	Unit
Power Dissipation Linear Derating Factor	(Notes 5 & 8)	P <sub>D</sub>	1.25		W mW/°C
			10		
	(Notes 5 & 9)		1.8		
	(Notes 6 & 8)		14.3		
Thermal Resistance, Junction to Ambient	(Notes 5 & 8)	R <sub>θJA</sub>	2.14		°C/W
	(Notes 5 & 9)		17.2		
	(Notes 6 & 8)		100		
Thermal Resistance, Junction to Lead	(Notes 5 & 9)	R <sub>θJL</sub>	70		°C/W
	(Notes 6 & 8)		58		
Operating and Storage Temperature Range		T <sub>J</sub> , T <sub>STG</sub>	-55 to +150		°C

- Notes:
- For a device surface mounted on 25mm x 25mm x 1.6mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions; the device is measured when operating in a steady-state condition.
  - Same as note (5), except the device is measured at t ≤ 10 sec.
  - Same as note (5), except the device is pulsed with D = 0.02 and pulse width 300μs.
  - For a dual device with one active die.
  - For a device with two active die running at equal power.
  - Thermal resistance from junction to solder-point (at the end of the drain lead).

## Thermal Characteristics (Continued)



**Electrical Characteristics** (Q1 N-Channel) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS</b> (Note 11)						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	40	—	—	V	V <sub>GS</sub> = 0V, I <sub>D</sub> = 250μA
Zero Gate Voltage Drain Current T <sub>J</sub> = +25°C	I <sub>DSS</sub>	—	—	1.0	μA	V <sub>DS</sub> = 40V, V <sub>GS</sub> = 0V
Gate-Source Leakage	I <sub>GSS</sub>	—	—	±100	nA	V <sub>GS</sub> = ±20V, V <sub>DS</sub> = 0V
<b>ON CHARACTERISTICS</b> (Note 11)						
Gate Threshold Voltage	V <sub>GS(th)</sub>	0.8	1.3	1.8	V	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	—	20	45	mΩ	V <sub>GS</sub> = 10V, I <sub>D</sub> = 3A
			33	60		V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 3A
Forward Transfer Admittance	Y <sub>fs</sub>	—	12.6	—	S	V <sub>DS</sub> = 5V, I <sub>D</sub> = 3A
Diode Forward Voltage (Note 11)	V <sub>SD</sub>	—	0.7	1.0	V	V <sub>GS</sub> = 0V, I <sub>S</sub> = 1A
<b>DYNAMIC CHARACTERISTICS</b> (Note 12)						
Input Capacitance	C <sub>iss</sub>	—	1790.8	—	pF	V <sub>DS</sub> = 20V, V <sub>GS</sub> = 0V, f = 1.0MHz
Output Capacitance	C <sub>oss</sub>	—	160.6	—	pF	
Reverse Transfer Capacitance	C <sub>rss</sub>	—	120.5	—	pF	
Gate Resistance	R <sub>g</sub>	—	1.03	—	Ω	V <sub>DS</sub> = 0V, V <sub>GS</sub> = 0V, f = 1MHz
Total Gate Charge	Q <sub>g</sub>	—	37.56	—	nC	V <sub>GS</sub> = 10V, V <sub>DS</sub> = 20V, I <sub>D</sub> = 3A
Gate-Source Charge	Q <sub>gs</sub>	—	7.8	—	nC	
Gate-Drain Charge	Q <sub>gd</sub>	—	6.6	—	nC	
Turn-On Delay Time	t <sub>D(on)</sub>	—	8.08	—	nS	V <sub>GS</sub> = 10V, V <sub>DS</sub> = 20V, I <sub>D</sub> = 3A
Turn-On Rise Time	t <sub>r</sub>	—	15.14	—	nS	
Turn-Off Delay Time	t <sub>D(off)</sub>	—	24.29	—	nS	
Turn-Off Fall Time	t <sub>f</sub>	—	5.27	—	nS	

**Electrical Characteristics** (Q2 P-Channel) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS</b> (Note 11)						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	-40	—	—	V	V <sub>GS</sub> = 0V, I <sub>D</sub> = -250μA
Zero Gate Voltage Drain Current T <sub>J</sub> = +25°C	I <sub>DSS</sub>	—	—	-1.0	μA	V <sub>DS</sub> = -40V, V <sub>GS</sub> = 0V
Gate-Source Leakage	I <sub>GSS</sub>	—	—	±100	nA	V <sub>GS</sub> = ±20V, V <sub>DS</sub> = 0V
<b>ON CHARACTERISTICS</b> (Note 11)						
Gate Threshold Voltage	V <sub>GS(th)</sub>	-0.8	-1.3	-1.8	V	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = -250μA
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	—	28	45	mΩ	V <sub>GS</sub> = -10V, I <sub>D</sub> = -3A
			30	60		V <sub>GS</sub> = -4.5V, I <sub>D</sub> = -3A
Forward Transfer Admittance	Y <sub>fs</sub>	—	16.6	—	S	V <sub>DS</sub> = -5V, I <sub>D</sub> = -3A
Diode Forward Voltage (Note 11)	V <sub>SD</sub>	—	-0.7	-1.0	V	V <sub>GS</sub> = 0V, I <sub>S</sub> = -1A
<b>DYNAMIC CHARACTERISTICS</b> (Note 12)						
Input Capacitance	C <sub>iss</sub>	—	1643.17	—	pF	V <sub>DS</sub> = -20V, V <sub>GS</sub> = 0V, f = 1.0MHz
Output Capacitance	C <sub>oss</sub>	—	179.13	—	pF	
Reverse Transfer Capacitance	C <sub>rss</sub>	—	127.82	—	pF	
Gate Resistance	R <sub>g</sub>	—	6.43	—	Ω	V <sub>DS</sub> = 0V, V <sub>GS</sub> = 0V, f = 1MHz
Total Gate Charge	Q <sub>g</sub>	—	33.66	—	nC	V <sub>GS</sub> = -10V, V <sub>DS</sub> = -20V, I <sub>D</sub> = -3A
Gate-Source Charge	Q <sub>gs</sub>	—	5.54	—	nC	
Gate-Drain Charge	Q <sub>gd</sub>	—	7.30	—	nC	
Turn-On Delay Time	t <sub>D(on)</sub>	—	6.85	—	nS	V <sub>GS</sub> = -10V, V <sub>DS</sub> = -20V, I <sub>D</sub> = -3A
Turn-On Rise Time	t <sub>r</sub>	—	14.72	—	nS	
Turn-Off Delay Time	t <sub>D(off)</sub>	—	53.65	—	nS	
Turn-Off Fall Time	t <sub>f</sub>	—	30.86	—	nS	

Notes: 11. Short duration pulse test used to minimize self-heating effect.  
12. Guaranteed by design. Not subject to production testing.

# Typical Characteristics (Q1 N-Channel)




Fig. 1 Typical Output Characteristic




Fig. 3 Typical On-Resistance vs. Drain Current and Gate Voltage




Fig. 5 On-Resistance Variation with Temperature




Fig. 2 Typical Transfer Characteristic




Fig. 4 Typical On-Resistance vs. Drain Current and Temperature




Fig. 6 On-Resistance Variation with Temperature




Fig. 7 Gate Threshold Variation vs. Ambient Temperature




Fig. 8 Diode Forward Voltage vs. Current




Fig. 9 Typical Total Capacitance




Fig. 10 Typical Leakage Current vs. Drain-Source Voltage




Fig. 11 Gate-Charge Characteristics




Fig. 12 Transient Thermal Response

# Typical Characteristics (Q2 P-Channel)




Fig. 13 Typical Output Characteristic




Fig. 15 Typical On-Resistance vs. Drain Current and Gate Voltage




Fig. 17 On-Resistance Variation with Temperature




Fig. 14 Typical Transfer Characteristic




Fig. 16 Typical On-Resistance vs. Drain Current and Temperature




Fig. 18 On-Resistance Variation with Temperature






Fig. 19 Gate Threshold Variation vs. Ambient Temperature




Fig. 20 Diode Forward Voltage vs. Current




Fig. 21 Typical Total Capacitance




Fig. 22 Typical Leakage Current vs. Drain-Source Voltage




Fig. 23 Gate-Charge Characteristics





Fig. 24 Transient Thermal Response

## Package Outline Dimensions

Please see AP02002 at <http://www.diodes.com/datasheets/ap02002.pdf> for the latest version.

### SO-8




SO-8		
Dim	Min	Max
A	-	1.75
A1	0.10	0.20
A2	1.30	1.50
A3	0.15	0.25
b	0.3	0.5
D	4.85	4.95
E	5.90	6.10
E1	3.85	3.95
e	1.27 Typ	
h	-	0.35
L	0.62	0.82
θ	0°	8°
All Dimensions in mm		

## Suggested Pad Layout

Please see AP02001 at <http://www.diodes.com/datasheets/ap02001.pdf> for the latest version.

### SO-8



Dimensions	Value (in mm)
X	0.60
Y	1.55
C1	5.4
C2	1.27

#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### **LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

**www.diodes.com**