

MF1050V-4

FOR DIGITAL MOBILE TELEPHONE, Rx

MF1050V-4

DESCRIPTION

This SAW filter for the receiving RF circuit of digital mobile communication equipment operating at 1477 MHz ~ 1501 MHz.

FEATURES

1. SMD package insures small size, lightweight.
2. Adjustment free.
3. Low insertion loss and high stop band attenuation.
4. Wide and sharp passband characteristics.
5. High stability and reliability.
6. Designed for reflow solderings.

APPLICATION

- Digital mobile cellular telephone
- Portable digital cellular telephone
- Wireless equipment


ELECTRICAL PERFORMANCE

Parameter	MF1050V-4			Units
	Min	Typ	Max	
PASSBAND FREQUENCY	1477 – 1501			MHz
PASSBAND CHARACTERISTICS				
Insertion Loss		2.5	3.5	dB
Ripple		0.6	1.5	dBp-p
VSWR		2.0	2.5	
STOPBAND ATTENUATION				
0 – 1050 MHz	40	48		dB
1050 – 1380 MHz	25	30		dB
1429 – 1453 MHz	15	18		dB
1542 – 1566 MHz	25	32		dB
1607 – 1631 MHz	40	45		dB
1737 – 1761 MHz	35	40		dB
1761 – 3000 MHz	23	27		dB

MAXIMUM RATINGS

Rating	Value	Unit
Input Power	40	mW
Operating Temperature Range	-20 to 75	°C
Storage Temperature Range	-30 to 85	°C

PACKAGE OUTLINE DIMENSIONS



DIMENSIONS ARE IN MILLIMETERS
±0.2 UNLESS OTHERWISE SPECIFIED

MF1050V-4 TYPICAL CHARACTERISTICS

