



211773-6 Product Details

Share Print Email



211773-6

TE Internal Number: 211773-6

Preliminary

View 3D PDF

CPC (Circular Plastic) and Circular Metal-Shell Connectors

Not reviewed for RoHS Compliance

Product Highlights:

- Housing
- Connector Style = Receptacle
- 19 Positions
- 19 Signal Positions
- 0 Power Positions

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- View Mating Products (2)
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- RECEPTACLE HOUSING, REVERSE SEX, SERIES I, SHELL SIZ... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version G)
- 3D Model (IGES, Version G)
- 3D Model (STEP, Version G)

List all Documents

Additional Information:

- Product Line Information

Additional Product Images:

- Contact Arrangement
- Keying Options

Related Products:

- Tooling
- Mating Products (2)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Connector Type = Housing
- Mount = Panel
- Mount Angle = Straight
- Shell Size = 23
- PCB Mount Retention = Without
- Shell Type = All Plastic
- Product Series = Series 1
- Thread Size = 1-3/8 - 18 UNEF-2A
- Sealed = Yes

Mechanical Attachment:

- Number of Power Positions = 0
- Mating Retention Type = Threaded Coupling
- VDE Tested = Yes
- Keying = A

Termination Features:

- Seal Type = Peripheral

Body Features:

- Number of Positions = 19
- Number of Signal Positions = 19
- Mount Style = Flange with Threaded Inserts

Contact Features:

- Contact Type = Socket
- Reverse Gender = Reverse

Housing Features:

- Connector Style = Receptacle
- Mating Alignment Type = Keyed
- Housing Material = Thermoplastic - GF
- Housing Color = Black
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Environmental Protection = With
- Reverse Numbering = Without

Industry Standards:

- RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance
- Lead Free Solder Processes = Not reviewed for lead free solder process

Environmental:

- Fluid Resistance = Immersion

Conditions for Usage:

- Accepts Wire Insulation Diameter, Range (mm [in]) = 3.81 [0.150]

Other:

- Brand = AMP

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Search Knowledge Base
Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

