

**General accessories**  
**BD 1 brass**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



Pressure-compensation elements ensure good ventilation of the enclosure and prevent the build-up of condensation while maintaining the appropriate IP class of protection.

**General ordering data**

|            |                                                                 |
|------------|-----------------------------------------------------------------|
| Order No.  | <a href="#">3080760000</a>                                      |
| Type       | BD 1 brass                                                      |
| Version    | Compensating element, Brass, External thread: M 20 x 1.5, IP 66 |
| GTIN (EAN) | 4032248011063                                                   |
| Qty.       | 1 pc(s).                                                        |

## General accessories

### BD 1 brass

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|        |       |            |      |
|--------|-------|------------|------|
| Length | 25 mm | Net weight | 92 g |
|--------|-------|------------|------|

### Approvals

|                          |                  |
|--------------------------|------------------|
| Approval for cable gland | Ex e II, II 2 GD |
|--------------------------|------------------|

### General information

|                                   |            |                                   |               |
|-----------------------------------|------------|-----------------------------------|---------------|
| AF size 1                         | 29 mm      | Cable gland                       | metric, brass |
| External thread                   | M 20 x 1.5 | Head diameter                     | 28 mm         |
| Length of thread                  | 10 mm      | Material                          | Brass         |
| O-Ring                            | NBR        | Operating temperature range, max. | 85 °C         |
| Operating temperature range, min. | -50 °C     |                                   |               |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000441    | UNSPSC     | 30-21-18-01 |
| eClass 4.1 | 27-14-12-96 | eClass 5.1 | 27-14-92-01 |
| eClass 6.0 | 27-14-91-09 | eClass 7.0 | 27-14-91-09 |

### Approvals

Approvals