


DO NOT SCALE

DIMENSIONS IN mm

METRIC


THIRD ANGLE

PROJECTION



NOTES:

- 1 FOR MINI-APPLICATOR CRIMPING.
2 FOR STANDARD-APPLICATOR CRIMPING.
3 FOR LOOSE-PIECE VERSIONS SEE DWG. 166296
4 UNDERCOATING: 1,3µm Ni.
SELECTIVE : 0,8µm Au.
ZONE I : BRIGHT TIN/LEAD PLATED.
5 UNDERCOATING: 1,3µm Ni.
SELECTIVE : 2,0µm Au.
REMAINDER : GOLDFLASH.



WIRE RANGE :
(0,2-0,56 mm²) 20-24 AWG
INSULATION RANGE :
1,57 DIA. MAX.

SEE NOTE 5	STAINLESS STEEL	BRASS	166046-4	1
SEE NOTE 4			166046-3	2
SEE NOTE 4			166046-1	1
PLATING OF BODY	MATERIAL OF SLEEVE	MATERIAL OF BODY	PARTNUMBER	

CUSTOMER DRAWING					FOR REFERENCE ONLY WILL NOT BE UPDATED				
© COPYRIGHT 19- BY AMP HOLLAND B.V.					ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.				
THIS DRAWING IS UNPUBLISHED					RELEASED FOR PUBLICATION				
AMP					AMP HOLLAND B.V. s-Hertogenbosch, The Netherlands.				
NAME					CONTACT ASSEMBLY-PIN TYPE XI, SIZE 20				
G	EH-0077-92	JvL	CvT	04-03-94	DWG. No. C-166046				
LTR.	REVISION RECORD	DR.	CHK.	DATE	REV. LTR. SHEET				
DR. J.V. LIEMPT	CHK. C.V. TILBURG	APP. J.V. SOEST	DATE: 08-02-93		G		1 OF 1		A3
DATE: 6 JAN 1993	DATE: 08-02-93	DATE: 08-02-93							