

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD

0

REVISED PER 0G3B-0933-03

12/5/03

SS

SRY

PHYSICAL PROPERTIES:

HOUSING: POLYPROPYLENE, UL94V-0, BLACK.

TERMINALS: BRIGHT TIN OVER COPPER ALLOY.

SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.

PITCH (TERMINAL SPACING): .375"




OPERATING TEMP.: 105° C MAX

ELECTRICAL PROPERTIES:

RATED CURRENT: 20A

OPERATING VOLTAGE: 300V

WIRE RANGE: 12-22 AWG

THIS PRINT IS
PRELIMINARYPRIOR TO CUSTOMER ORDER
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

1.125	4	BC6-Q108-04	1546868-4
.375	2	BC6-Q108-02	1546868-2
DIM. A	NO. OF POS.	CATALOG NUMBER	TYCO PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. SCHLEGEL 12/5/03

CHK S. YODER 12/5/03


APVD S. YODER 12/5/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
INCHES

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± .01
3 PLC ± .005
4 PLC ± -
ANGLES ± -

FINISH

BUCHANAN

Tyco Electronics Corporation

City, State, Zip

NAME

BC6-Q108-XX ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1546868

SCALE NTS

SHEET 1 OF 1

REV 0