




CRYSTEK
CRYSTALS
A DIVISION OF CRYSTEK CORPORATION

CVPD-034 LVPECL
Voltage Controlled Crystal Oscillator
5×7mm SMD
3.3 Volts



Rev: X
Date: 24-Sep-2014
Page 1 of 3



CRYSTEK
CORPORATION

12730 COMMONWEALTH DRIVE • FORT MYERS, FLORIDA 33913
PHONE: 239-561-3311 • 800-237-3061
FAX: 239-561-1025 • WWW.CRYSTEK.COM

CVPD-034 LVPECL
Voltage Controlled Crystal Oscillator
5×7mm SMD
3.3 Volts



Frequency Range:	77.760 MHz to 200.000 MHz
Frequency Pulling (APR*) Min.:	±50ppm
Temperature Range: (standard)	0°C to +70°C
(Option M)	-20°C to +70°C
(Option X)	-40°C to +85°C
Storage:	-45°C to 90°C
Input Voltage:	3.3V ±5%
Control Voltage:	1.65V ±1.65V
Input Current:	55mA Typical, 88mA Max
Output:	Differential LVPECL
Symmetry:	45/55% Max @ zero crossing point
Rise/Fall Time:	1nSec Max (20% to 80%)
Linearity:	±10% Max
Logic: Terminated to Vdd-2V into 50 Ω	
Temp. 0°C to 85°C	"0"=1.490 Min, 1.680 Max
	"1"=2.275 Min, 2.420 Max
Temp. -40°C to 0°C	"0"=1.490 Min, 1.745 Max
	"1"=2.215 Min, 2.420 Max
Disable Time:	200nSec Max
Enable Time:	20uSec Max
Phase Jitter: 12kHz~80MHz	0.5pSec Typical, 1pSec RMS Max
Phase Noise: 10Hz	-70dBc/Hz Typical
100Hz	-98dBc/Hz Typical
1kHz	-125dBc/Hz Typical
10kHz	-145dBc/Hz Typical
100kHz	-149dBc/Hz Typical
Sub-harmonics:	None
Aging:	<5ppm 1st year, <2ppm every year thereafter

*** Inclusive of calibration, frequency stability, and aging**

Rev: X
Date: 24-Sep-2014
Page 2 of 3

CVPD-034 LVPECL

Voltage Controlled Crystal Oscillator

5×7mm SMD

3.3 Volts

Crystek Part Number Guide

CVPD - 034 X - 50 - 155.520

#1 #2 #3 #4 #5

#1 Crystek PECL VCXO
#2 Model 034
#3 Temp Range: Blank = 0/70°C, M = -20/70°C, X = -40/85°C
#4 Pullability: (see Table 1)
#5 Frequency in MHz: 3 or 6 decimal places

Pullability Indicator

50 ± 50ppm

Table 1

Example:

CVPD-034X-50-155.520

3.3V, -40/85°C, ±50ppm (APR), 155.520 MHz

Standard Frequencies

(±50ppm, 0/70°C)
77.760 MHz
155.520 MHz
156.250 MHz
161.132800 MHz
200.000 MHz


Mechanical:

Shock: MIL-STD-883, Method 2002, Condition B
Solderability: MIL-STD-883, Method 2003
Vibration: MIL-STD-883, Method 2007, Condition A
Solvent Resistance: MIL-STD-202, Method 215
Resistance to Soldering Heat: MIL-STD-202, Method 210, Condition I or J


Environmental:

Thermal Shock: MIL-STD-883, Method 1011, Condition A
Moisture Resistance: MIL-STD-883, Method 1004

RECOMMENDED REFLOW SOLDERING PROFILE




NOTE: Reflow Profile with 240°C peak also acceptable.




Dimensions inches (mm)

All dimensions are Max unless otherwise specified.




Tristate Function

Function pin 2	Output pin
Open or N/C	Active
"1" level 0.7×Vdd Min	Active
"0" level 0.3×Vdd Max	High Z



SUGGESTED PAD LAYOUT



0.01μF Bypass Capacitor Recommended

PIN	Connection
1	Volt Control
2	Enable/Disable
3	GND
4	Output
5	Comp Output
6	Vcc

Rev: X

Date: 24-Sep-2014

Page 3 of 3