


10		9		8		7		6		5		4		3		2		19005	
MATERIAL NUMBER LOOSE PIECE	ENGRNG NUMBER LOOSE PIECE	MATERIAL NUMBER MYLAR TAPE	ENGINEERING NUMBER MYLAR TAPE	MATERIAL NUMBER CONTINUOUS STRIP	ENGINEERING NUMBER CONTINUOUS STRIP	WIRE RANGE AWG	ACCEPTS MALE TAB SIZE	COLOR	STOCK THKNS (REF)	A MAX	B MAX	C MAX	D MWID	E MIN	T REF				
190050001	AA-2261	190050004	AA-2261T	190050003	AA-2261C	22- 18	.250x.032/6.35x0.81	RED	.018/0.46	.89/22.6	.38/9.7	.23/5.9	.16/4.1	.08/2.0	.52/13.2				
190050005	BB-2263	190050009	BB-2263T	190050008	BB-2263C	16- 14	.250x.032/6.35x0.81	BLUE	.018/0.46	.89/22.6	.38/9.7	.23/5.9	.16/4.1	.08/2.0	.52/13.2				
190050010	C-2265	190050015	C-2265T	190050014	C-2265C	12- 10	.250x.032/6.35x0.81	YELLOW	.018/0.46	1.04/26.4	.38/9.7	.34/8.7	.27/6.8	.14/3.5	.51/13.0				



- NOTES:
1. TERMINAL MATERIAL: BRASS
 2. TERMINAL FINISH: TIN PLATED
 3. INSULATION MATERIAL: MOLDED NYLON
 4. MWID = MAXIMUM WIRE INSULATION DIAMETER
 5. PARTS ARE ROHS COMPLIANT.

ADD CONTINUOUS STRIP EC NO: IPG2014-1666 DRAWING: GR0JAS01 2014/04/03 CHKD: JMACNEIL APPR: JMACNEIL 2014/04/21	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
		▽=0	mm	INCH	DRAWN BY	DATE	TITLE FULLY INSULATED FEMALE COUPLER				
		▽=0	4 PLACES ± --- ± ---	3 PLACES ± --- ± ---	EMF	1993/06/25					
		2 PLACES ± --- ± ---	CHECKED BY	DATE							
		1 PLACE ± --- ± ---	---	---							
C	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	ANGULAR ± ---°		APPROVED BY		DATE	MOLEX MOLEX INCORPORATED			
					JMACNEIL		2010/03/19				
					MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
				SEE CHART		SD-19005-001		1 OF 1			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											