


# SPECIFICATIONS

Part Number: 19032526A    SPEC Number: 26016815A  
 Model Number: MS24B3    April 20, 2012



## Mechanical Drawing:



### Motor:

Nominal Voltage	= 24 vdc
Operating Voltage Range	= 12 - 28 vdc
Nominal Running Current	= 0.290 amps
Max. Locked Rotor Current	= 0.730 amps
Running Power	= 7.0 watts
Average Speed	= 2900 RPM
Bearings	= Ball
Air Flow	= 110 CFM
Acoustics	= 49.1 dBA

### Construction:

Venturi: Plastic, Black, UL 94V-0.  
 Propeller: Plastic, Black, UL 94V-0

### Life Expectancy:

This fan is designed for continuous duty life of 85,000 hours at 40°C.

### Additional Features:

Brushless DC Motor	
Polarity Protected	
Automatic Reset Capability	
Locked Rotor Protection	
Operating Temperature:	-10°C to 70°C
Storage Temperature	-40°C to 85°C

### Termination:

12" Lead wires, 22 AWG, UL 1061  
 Red = Power (+)  
 Black = Ground (-)

### Agency Approvals:

UL, CUL