




DESCRIPTION: FEMALE - 0.283 RIGHT ANGLE / MACHINED - ECONOMY



MATERIAL:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-O RATED, WHITE PA6T
PROCESS TEMP.: 260° PROCESS TEMPERATURE
CONTACT: BRASS
SEALING MATERIAL: F04 FLEXIBLE ADHESIVE

ELECTRICAL:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOhms Max.
INSULATION RESISTANCE: 1,000 MOhms min.
VOLTAGE: 500VAC FOR 1 MINUTE
TEMPERATURE: -50° C TO 100° C

RoHS COMPLIANT

No. OF PINS	DIMENSIONS							
	A	B	C	D	E	F	G	H
9	1.213	0.984	0.642	0.311	0.236	0.756	0.496	0.427
	30.80	24.99	16.30	7.90	5.99	19.20	12.60	10.85
15	1.541	1.312	0.970	0.311	0.236	1.091	0.496	0.427
	39.15	33.32	24.65	7.90	5.99	27.70	12.60	10.85
25	2.087	1.852	1.512	0.311	0.236	1.618	0.496	0.427
	53.00	47.04	38.40	7.90	5.99	41.10	12.60	10.85




MEETS IP67 STANDARDS
(SEE PAGE 3 FOR SEALING DETAILS)

773-EYY-213RYY1

SERIES
POSITIONS
E09
E15
E25
GENDER
2 = FEMALE
TERMINATION
1 = PC MOUNTING
SHELL PLATING
3 = NICKEL
RoHS COMPLIANT
HARDWARE OPTIONS
00 = NO HARDWARE
01 = .065" CLINCH NUT (BOARD SIDE)
14 = SHORT BRACKET WITH 4-40 SCREWLOCK
46 = BRACKET WITH 4-40 INSERT AND BOARDLOCK
PLATING OPTIONS
1 = GOLD FLASH
2 = 30MICRO-INCH GOLD

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: M. SIGMON		DATE: 07-26-12			
			CHECKED:		DATE:			
			SCALE: 1:1	SHEET 1 OF 4	REV 3			
			DWG NO. 773-EYY-213RYY1					



*** TYP. ON ALL SIZES**


DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: M. SIGMON		DATE: 07-26-12	
			CHECKED:		DATE:	
NorComp			SCALE: FULL		SHEET OF 2 4	
			DWG NO. 773-EYY-213RYY1		REV 3	



FRONT SEAL APPLIED BETWEEN
FRONT INSULATOR AND
FRONT METAL SHELL

MIDDLE SEAL APPLIED BETWEEN
FRONT INSULATOR AND
BACK INSULATOR



DETAIL A-A



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: M. SIGMON		DATE: 07-26-12	
		CHECKED:		DATE:	
	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 2.5 : 1	SHEET 3 OF 4		REV 3
		DWG NO. 773-EYY-213RYY1			


HARDWARE OPTIONS 14 = SHORT BRACKET & 4-40 SCREW LOCK

01 CLINCH NUT OPTION

01X 0.065" (BOARD SIDE) - CN1





MOUNTING BRACKET





SCREW LOCK

46 = BRACKET WITH 4-40 INSERT AND BOARDLOCK



HOLE C/L 0.339



MOUNTING BRACKET WITH BOARD LOCK

BRACKETS MOUNTED ON CONNECTOR

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 06-10-09		
		CHECKED:		DATE:		
		SCALE: N.T.S.	SHEET 4		OF 4	REV 3
		DWG NO. 773-EYY-213RYY1				