










ケース取付け穴推奨寸法 (コネクタ取付け面)
RECOMMENDED CASE OPENING DIMENSION (CONNECTOR SIDE)

プラグ側部品構成 PLUG SIDE PARTS CONSTRUCTION		項番 NUMBER	材質 MATERIAL	仕上げ FINISH
プラグ ハウジング アッセンブリ PLUG HS'G ASS'Y 55833-****	プラグ ハウジング PLUG HS'G	①	ガラス入りポリエステル(PBT) UL94V-0、色:黒	—
	インナーハウジング INNER HS'G	②	ガラスなしポリエステル(PBT) UL94V-0、色:黒、白、灰	—
	M2 ナットサート M2 NUTSERT	③	黄銅 BRASS	ニッケルメッキ:2μm MIN. NICKEL PLATING
	グラウンドターミナル GROUND TERMINAL	④	りん青銅 PHOSPHOR BRONZE	錫メッキ:1μm MIN. TIN PLATING
	アッパラーバー UPPER RUBBER	⑤	ニトリルゴム、色:黒 NITRILE RUBBER	—
	ロアラーバ LOWER RUBBER	⑥	ニトリルゴム、色:黒 NITRILE RUBBER	—
別売り品 ANOTHER SALES GOOTS	クリンピン CRIMP PIN	⑦	詳細は、56160-8****のセールス図面を参照して下さい。 REFER TO THE 56160-8*** S.D ON DETAILS	
お客様調達品 CUSTOMER PROCUREMENT GOOTS	M2 十字穴付きなべ小ねじ M2 CROSS RECESSED HEAD SCREW	⑧	JIS B 1111-M2xL 耐腐蝕規格十字穴付き小ねじ	
	止め金具 (六角ナット) STOP METAL FITTINGS (HEXAGON NUT)	⑨	M2 タップ立て等にて可	



実装状態図
MOUNTING STATE

① プラグ ハウジング
PLUG HS'G

② インナーハウジング
INNER HS'G

③ M2 ナットサート
M2 NUTSERT

④ グラウンドターミナル
GROUND TERMINAL

⑤ アッパラーバー
UPPER RUBBER

⑥ ロアラーバ
LOWER RUBBER


⑦ クリンピン
CRIMP PIN

⑧ M2 十字穴付きなべ小ねじ
M2 CROSS RECESSED HEAD SCREW

⑨ 止め金具 (六角ナット)
STOP METAL FITTINGS (HEXAGON NUT)

RELEASED EC NO: J2008-4369 DRWN:MABEI CHKD:KTOYODA APPR:NUKITA 0	DESCRIPTION 2008/06/26 2008/06/26 2008/06/26	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
					MM ONLY		5:1	METRIC		
			10 UNDER	± 0.2	DRAWN BY M. NABEI	DATE '08/06/23	TITLE SMEC(SERVO MOTOR ENCODER CONN.) PLUG HS'G ASS'Y			
			10 OVER 30 UNDER	± 0.25	CHECKED BY K. TOYODA	DATE '08/06/23				
			30 OVER	± 0.3	APPROVED BY N. UKITA	DATE '08/06/23			 MOLEX INCORPORATED	
			ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.	SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-55833-004		2 OF 3				
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								


F
E
D
C
B
A




嵌合相手 MATING SMEC REC.
リセプラグ キット : 54346-007*
RECEPTACLE KITS
詳細は、セールス図面を参照して下さい。
REFER TO THE S.D ON DETAILS

グラントコンタクト
GROUND CONTACT


リセ ターミナル : 56161-8***
REC.TERMINAL
詳細は、セールス図面を参照して下さい。
REFER TO THE S.D ON DETAILS



断面 F-F
SECTION F-F



断面 E-E
SECTION E-E





グラントターミナル
GROUND TERMINAL

リセ シェルボディ
REC.SHELL BODY

断面 C-C
SECTION C-C

嵌合状態図
CROSS-SECTION VIEW OF MATED CONNECTORS
(SCALE : 4-1)
*本図は、7 極品を示す。
THIS DRAWING 7CIRCUIT GOODS.



断面 D-D
SECTION D-D

RELEASED EC NO: J2008-4369 DRWN: NABEI CHKD: KTOYODA APPR: NUKITA REV 0	DESCRIPTION 2008/06/26 2008/06/26 2008/06/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	DRAWN BY M. NABEI	DATE '08/06/23	TITLE SMEC(SERVO MOTOR ENCODER CONN.) PLUG HS'G ASS'Y				
		10 OVER 30 UNDER	±0.25	CHECKED BY K. TOYODA	DATE '08/06/23					
		30 OVER	±0.3	APPROVED BY N. UKITA	DATE '08/06/23	MOLEX INCORPORATED				
		ANGULAR ±3 °		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-55833-004			SHEET NO. 3 OF 3	
	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

55833-0771