



BA9s, 18-30V buzzer, cont. tone

Part no.
Article no.

M22-XAM
229025

83 dB/10 cm, 18 - 30 mA, positive pole connected to X1, f = 2300 Hz

Program

Range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Single unit/Complete unit			Single unit
Description			83 dB/10 cm, 18 - 30 mA, positive pole at X1, f = 2300 Hz
Function			Continuous tone, 18 - 30 V AC/DC
Front ring			Front ring: titanium
For use with			BA9s base
Connection to SmartWire-DT			no

Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	012528
CSA Class No.	3211-03
NA Certification	UL listed, CSA certified

Technical data according to ETIM 4.0

Operational voltage at DC			0
Type of acoustic signal			Continuous tone
Voltage type			AC/DC
Operating voltage at AC 60 Hz		V	24
Operating voltage at AC 50 Hz		V	24

CAD-Data

Product standards CAD data: <http://eaton-moeller.partcommunity.com>

Additional product information (links)

Engineering

Key to part numbers	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/TYPENSCHLUESSEL_RM-Q-TITAN_de.pdf
Engineering	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/PRO_RMQTitan_D_de.pdf
Ordering example for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Bestellbeispiel_F0315_COMBINATION_de.pdf
Order form for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf