



Technical drawing of a mechanical part showing dimensions and a feature callout. The drawing includes the following dimensions and features:

- Overall width: 2,54
- Overall height: 10,67
- Horizontal dimensions from the left edge:
 - 16,65
 - 5,49
 - 2,74
 - 1,37
 - 4,11
 - 6,86
 - 9,6
- Horizontal dimensions from the right edge:
 - 8,23
- Vertical dimension from the top edge to the centerline: 9,4
- Feature callout: $\phi 1$ (Feature 1) pointing to a hole.
- Feature numbers: 15, 9, 8, 1

Mating Cycles	500
Filter type	C
Capacitance	47pF±20%
Working Voltage	100V
Current Rating	7,5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION dB
5	-
10	-
50	-
100	-
500	30dB
1000	35dB

							Dat.	Name		D-Sub, male, angled, 15 Poles, turned solder pins, tin plated shell with dimples, brackets and clinch nuts	Mo?Ms Lab/ Scale 1.5:1	
						Detail.	8-JUL-02	CV				
						Insp.						All Dim. in mm
						Stand.						Orig. Size DIN A 4
09642247217	M3		33269	22/11/05	JMDR	HARTING EURL F-95972 Paris				TB 0964224721x	Blatt / Page 3 / 4	
09642247216	UNC 4-40		31058	8-JUL-02	CV							
Part number	Nut thread		Mod.	Dat.	Name							