

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

PHYSICAL PROPERTIES:

HOUSING MATERIAL: THERMOPLASTIC, PC

FLAMABILITY: UL94V-0

COLOR: BLACK

TERMINAL:

TERMINALS: BRASS, TIN PLATED

SCREWS: 6-32 STEEL, NICKEL PLATED

MECHANICAL:

PITCH: .437

WIRE RANGE: 14-22 AWG

RECOMMENDED TIGHTENING

TORQUE: 12IN-LB

ELECTRICAL PROPERTIES:

MAX CURRENT: 25A

OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:

OPERATING TEMP: -40°C TO 120°C



MARKED WITH WHITE INK APPROX AS SHOWN.

2




SEE FIGURE.







PRELIMINARY PART NUMBER.





TE LOGO LOCATED APPROXIMATE
AREA SHOWN.

[illegible]


LOC	DIST	REVISIONS				
FT	0	P	LTR	DESCRIPTION	DATE	APVD
			—	SEE SHEET 1	—	—



3-1546671-0, 3-1546671-4



3-1546671-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHEGEL	4/4/03	 TE Connectivity					
		CHK C RICHARD	4/4/03						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C RICHARD	4/4/03	NAME DOUBLE ROW BARRIER STRIP W/ WIRE CLAMP, .437 SPACING					
	0 PLC ± -	PRODUCT SPEC		SIZE A3			CAGE CODE 00779	DRAWING NO C-1546671	RESTRICTED TO —
	1 PLC ± -	—							
	2 PLC ± .01	APPLICATION SPEC							
	3 PLC ± .005	—							
	4 PLC ± -	—							
	ANGLES ± 2'	—							
MATERIAL —	FINISH —	WEIGHT —							
CUSTOMER DRAWING				SCALE NTS	SHEET 3 OF 3	REV C14			