




DRAWING MADE IN THIRD ANGLE PROJECTION
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
CM	53											0	RELEASED PER PR CM 93-69	7-14-93	LS	RS	

16.76	.660
2.79	.110
2.67	.105
2.41	.095
2.29	.090
2.24	.088
2.16	.085
2.06	.081
2.01	.079
1.93	.076
1.91	.075
1.57	.062
1.52	.060
1.40	.055
1.37	.054
1.02	.040
0.63	.025
0.38	.015
0.20	.008
0.13	.005
MM	IN
CONVERSION TABLE	

PRE-TIN	0.20 BRASS	1.52 MAX	0.2 - 0.5 mm ² (30-24 AWG)	794019-1
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 3 PLC DEC ± - ANGLES ± 0°30'		DR 7-14-93 L. SMITH CHK 7-14-93 R. SWING APPD 7-15-93 C. CASH APPD 7-15-93 C. CASH	NAME AMP AMP INCORPORATED Hanleburg, Pa. 17105	
SEE TABLE		PRODUCT SPEC -	.062 SOCKET, LOOSE PIECE, COMMERCIAL PIN & SOCKET	
FINISH SEE TABLE		APPLICATION SPEC -	SIZE D 00779	DRAWING NO 794019
		WEIGHT -	SCALE 5:1	SHEET 1 OF 1

METRIC