




- Designed for RF Front-end Applications
- Excellent Rejection
- 1.45 x 1.15 mm Surface-mount Case
- Complies with Directive 2002/95/EC (RoHS)



**SF2217K**

**1591.5 MHz  
SAW Filter**



**SM1411-5 Case**

## Absolute Maximum Ratings

| Rating                                                     | Value      | Units |
|------------------------------------------------------------|------------|-------|
| Maximum Incident Power in Passband                         | +10        | dBm   |
| Maximum DC Voltage On any Non-ground Terminal              | 3          | VDC   |
| Operating Temperature Range                                | -40 to +85 | °C    |
| Storage Temperature Range in Tape and Reel                 | -40 to +85 | °C    |
| Soldering Temperature Profile, 5 cycles/10 seconds maximum | 265        | °C    |

## Electrical Characteristics

| Characteristic                                     | Sym        | Notes | Min      | Typ   | Max   | Units             |
|----------------------------------------------------|------------|-------|----------|-------|-------|-------------------|
| Center Frequency                                   | $f_c$      |       | 1591.5   |       |       | MHz               |
| Insertion Loss, 1574 to 1609 MHz                   | $IL_{MAX}$ |       |          | 2.4   | 3.7   | dB                |
| Amplitude Ripple, 1574 to 1609 MHz                 |            |       |          | 1.3   | 2.6   | dB <sub>P-P</sub> |
| Group Delay Ripple, 1574 to 1609 MHz               |            |       |          | 17    | 50    | ns <sub>P-P</sub> |
| Rejection Referenced to 0 dB:                      |            |       |          |       |       | dB                |
| 10 to 1200 MHz                                     |            |       | 28       | 34    |       |                   |
| 1200 to 1450 MHz                                   |            |       | 28       | 34    |       |                   |
| 1450 to 1540 MHz                                   |            |       | 20       | 37    |       |                   |
| 1626 to 1710 MHz                                   |            |       | 9        | 31    |       |                   |
| 1710 to 2000 MHz                                   |            |       | 30       | 37    |       |                   |
| 2000 to 2500 MHz                                   |            |       | 30       | 37    |       |                   |
| VSWR, 1574 to 1609 MHz                             |            |       |          | 2.0:1 | 2.4:1 |                   |
| Terminating Source impedance                       | $Z_S$      |       |          | 50    |       | $\Omega$          |
| Terminating Load impedance                         | $Z_L$      |       |          | 50    |       | $\Omega$          |
| Case Style                                         |            |       | SM1411-5 |       |       |                   |
| Lid Symbolization □= year/month manufacturing code |            |       | B□       |       |       |                   |





**CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.**


### Notes:

1. US and international patents may apply.
2. RFM, stylized RFM logo, and RF Monolithics, Inc. are registered trademarks of RF Monolithics, Inc.


## Frequency Response Plots





## Input VSWR Plot



## Output VSWR Plot



# SM1411-5 1.4 X 1.1 mm 5-Terminal Surface-mount Case Drawing




**PCB Footprint**

## Case and PCB Footprint Dimensions


| Dimension | mm     |        |        | Inches |        |        |
|-----------|--------|--------|--------|--------|--------|--------|
|           | Min    | Nom    | Max    | Min    | Nom    | Max    |
| A         | 1.3500 | 1.4000 | 1.4500 | 0.0531 | 0.0551 | 0.0571 |
| B         | -      | 0.0750 | -      | -      | 0.0030 | -      |
| C         | 0.1700 | 0.250  | 0.3300 | 0.0067 | 0.0098 | 0.0130 |
| D         | 1.0500 | 1.1000 | 1.1500 | 0.0413 | 0.0433 | 0.0453 |
| E         | -      | 0.2875 | -      | -      | 0.0113 | -      |
| F         | 0.2450 | 0.3250 | 0.4050 | 0.0096 | 0.0128 | 0.0159 |
| G         | -      | 0.100  | -      | -      | 0.0039 | -      |
| H         | -      | 0.5000 | -      | -      | 0.0197 | -      |
| I         | 0.6000 | 0.6500 | 0.700  | 0.0236 | 0.0256 | 0.0276 |
| J         | -      | 1.3500 | -      | -      | 0.0531 | -      |
| K         | -      | 0.3500 | -      | -      | 0.0138 | -      |
| L         | -      | 0.1500 | -      | -      | 0.0059 | -      |
| M         | -      | 0.2875 | -      | -      | 0.0113 | -      |
| N         | -      | 0.4250 | -      | -      | 0.0167 | -      |
| O         | -      | 1.0000 | -      | -      | 0.0394 | -      |

| Materials          |                                                          |
|--------------------|----------------------------------------------------------|
| Solder Pad Plating | 0.3 to 1.0 $\mu$ m Gold over 1.27 to 8.89 $\mu$ m Nickel |
| Lid Plating        | 2.0 to 3.0 $\mu$ m Nickel                                |
| Body               | Al <sub>2</sub> O <sub>3</sub> Ceramic                   |
| Pb Free            |                                                          |

## Test Circuit



## Reel Dimensions - 7 inch Reel, 3000 Filters



## Tape Dimensions

