

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

120066-1034

Status:

Active

Overview:

Brad® Micro-Change® (M12) Connectors

Description:

Micro-Change® (M12) Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 18 AWG, TPE Cable, 1.0m (3.28') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E152210

General

Product Family

Industrial Cordsets

Series

120066

Connector End A

Micro-Change® (M12)

Connector End B

Micro-Change® (M12)

IP Rating

IP67

Overview

Brad® Micro-Change® (M12) Connectors

Product Name

Micro-Change® (M12)

Protocol

N/A

Region

America

Type

Double Ended

UPC

78678837454

Physical

Cable Diameter

6.86mm (.270")

Cable Length

1.0m (3.28')

Color - Cable Jacket

Yellow

Coupling Style

Threaded

Gender

Female-Male

Keyway

Single

LED Indicator

No

Material - Cable Jacket

TPE

Material - Connector Body

TPE

Material - Contact

Copper Alloy

Material - Coupling Nut

Nickel-plated Brass

Material - O-Ring

Viton

Material - Plating Mating

Gold over Nickel

Net Weight

185.830/g

Orientation

Straight

Poles

5

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

18

Wire/Cable Type

PLTC-ER

Electrical

Current - Maximum per Contact

4A

Voltage - Maximum

250V AC/DC

Material Info

Old Part Number

885030K03M010

Reference - Drawing Numbers

Sales Drawing

SD-120066-020



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

120066Series

This document was generated on 10/15/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**