


929924-2 Product Details

[Share](#) [Print](#) [Email](#)


929924-2

TE Internal Number: 929924-2

 **Active**

 [View 3D PDF](#)

Timer Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact
- Contact Type = Socket
- Standard Power-Timer Series
- Wire Range = 2.50-4.00² [13-11] mm [AWG]
- Accepts Wire Insulation Diameter, Range = 3.40 - 3.71 mm

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [STANDARD POWER TIMER CONTACT Standard Power Timer Ko...](#) (TIF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A11)
- [3D Model](#) (IGES, Version A11)
- [3D Model](#) (STEP, Version A11)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Line Drawing](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- Series = Standard Power-Timer
- Mating Area Interface Dimensions (mm [in]) = 4.75 x 0.81 [.187 x .032]
- [Wire/Cable Type](#) = Regular Wire
- Insulation Support = With

Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 2.50-4.00² [13-11]
- Single Wire Sealing System = Yes
- Insulation Type = FLR (Thin Walled Cable)
- Cantilever Spring Material = Stainless Steel
- Single Seal Part No. = 963245-1

Contact Features:

- Contact Type = Socket
- [Contact Base Material](#) = CuSn4
- [Contact Plating, Mating Area, Material](#) = Pre-Tin

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Accepts Wire Insulation Diameter, Range \(mm \[in\]\)](#) = 3.40 - 3.71 [0.134 - 0.146]
- [Applies To](#) = Wire/Cable

Operation/Application:

- Cavity Plug Part No. = 100132-1

Packaging Features:

- [Packaging Method](#) = Loose Piece

Other:

- GET 0.64 Connector System = No
- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

