




	1	2	3	4	5	6	7																																																																															
A	Material ①Clamp: Brass,Ni plated ②Terminal screw: Steel Zinc plating "-" slot type ③Wire guard solder pin: Brass,Tin plated ④Terminal housing: Thermoplastic (UL94V-0) , GREEN Electrical cULus Voltage rating:300VAC Current rating:8A Wire range: Solid wire(AWG):16-24 Stranded wire(AWG):16-24 Torque(Lb-In):2.17 Screw: M2 Wire strip length:6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval: 							A																																																																														
B	 							B																																																																														
C								C																																																																														
D	DIMENSION <table><tr><td>L</td><td>(N-1)x3.81+4.55</td></tr><tr><td>P</td><td>(N-1)x3.81</td></tr></table> N=Number of poles <table><tr><td>Poles</td><td>Tolerance</td></tr><tr><td></td><td>DIM L&DIM P</td></tr><tr><td>2p-4p</td><td>±0.15</td></tr><tr><td>5p-8p</td><td>±0.25</td></tr><tr><td>9p-16p</td><td>±0.30</td></tr><tr><td>17p-24p</td><td>±0.35</td></tr></table>							L	(N-1)x3.81+4.55	P	(N-1)x3.81	Poles	Tolerance		DIM L&DIM P	2p-4p	±0.15	5p-8p	±0.25	9p-16p	±0.30	17p-24p	±0.35	D																																																														
L	(N-1)x3.81+4.55																																																																																					
P	(N-1)x3.81																																																																																					
Poles	Tolerance																																																																																					
	DIM L&DIM P																																																																																					
2p-4p	±0.15																																																																																					
5p-8p	±0.25																																																																																					
9p-16p	±0.30																																																																																					
17p-24p	±0.35																																																																																					
E								E																																																																														
F								F																																																																														
G	RECOMMENDER PCB LAYOUT RoHS compliant <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>Alex</td><td></td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td></td><td>Approved</td><td>Hellwig</td><td></td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±1°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>①</td><td>Drawn</td><td>19.04.2010</td><td>Alex</td><td colspan="3" rowspan="2">  </td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td></tr></table>							Scale	1:1					Date	Name	Customer-No.	TOLERANCE						Drawn	Alex		X.	±0.50					Approved	Hellwig		X.X	±0.30								X.XX	±0.10								DIM	TOL								X.°	±1°										①	Drawn	19.04.2010	Alex				Angle	TOL	Id.	Modification	Date	Name	G
Scale	1:1					Date	Name	Customer-No.																																																																														
TOLERANCE						Drawn	Alex																																																																															
X.	±0.50					Approved	Hellwig																																																																															
X.X	±0.30																																																																																					
X.XX	±0.10																																																																																					
DIM	TOL																																																																																					
X.°	±1°																																																																																					
		①	Drawn	19.04.2010	Alex																																																																																	
Angle	TOL	Id.	Modification	Date	Name																																																																																	
H	ASSMANN WWSW components Drawing-No. ASS 4109 CO Replace rev00 Sheet							H																																																																														
	1	2	3	4	5	6	7																																																																															