




Single and Dual In-Line Resistor Networks



The model 4600 is a conformal coated and the model 4300 is a molded single in-line package resistor networks. Their low profile is compatible with DIPs. They are recommended for rosin flux and solvent clean or no clean flux processes. The 4100 series is a molded dual in-line network. Gold Epoxy provides excellent marking contrast for permanent laser marking on all three series. All are compatible with automatic insertion equipment. All are also available in additional values, dual terminators, additional pin count and additional profiles. Call for quote. Manufacturer's literature available upon request.

11

| Stock No. | Mfr.'s Type       | Ohms    | Circuit  | Pin Count | Watts | EACH |       |       |       |
|-----------|-------------------|---------|----------|-----------|-------|------|-------|-------|-------|
|           |                   |         |          |           |       | 1-9  | 10-24 | 25-49 | 50-99 |
| 755-4721  | 4114R-1-102       | 1K      | Isolated | 14        | 2.00  | .45  | .43   | .42   | .40   |
| 755-4734  | 4114R-1-103       | 10K     | Isolated | 14        | 2.00  | .48  | .44   | .40   | .38   |
| 755-4711  | 4114R-1-15        | 150     | Isolated | 14        | 2.00  | .48  | .44   | .40   | .38   |
| 755-4713  | 4114R-1-22        | 220     | Isolated | 14        | 2.00  | .45  | .41   | .38   | .36   |
| 755-4715  | 4114R-1-331       | 330     | Isolated | 14        | 2.00  | .49  | .44   | .41   | .39   |
| 755-4934  | 4114R-2-103       | 10K     | Bussed   | 14        | 2.00  | .48  | .44   | .40   | .38   |
| 755-4930  | 4114R-2-472       | 4.7K    | Bussed   | 14        | 2.00  | .48  | .44   | .40   | .39   |
| 755-4809  | 4116R-1-101       | 100     | Isolated | 16        | 2.25  | .48  | .44   | .40   | .39   |
| 755-4821  | 4116R-1-102       | 1K      | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4834  | 4116R-1-103       | 10K     | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4847  | 4116R-1-104       | 100K    | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4811  | 4116R-1-151       | 150     | Isolated | 16        | 2.25  | .46  | .41   | .38   | .37   |
| 755-4838  | 4116R-1-203       | 20K     | Isolated | 16        | 2.25  | .48  | .44   | .40   | .39   |
| 755-4813  | 4116R-1-221       | 220     | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4826  | 4116R-1-222       | 2.2K    | Isolated | 16        | 2.25  | .48  | .44   | .40   | .39   |
| 755-4814  | 4116R-1-271       | 270     | Isolated | 16        | 2.25  | .49  | .45   | .41   | .40   |
| 755-4803  | 4116R-1-330       | 33      | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4815  | 4116R-1-331       | 330     | Isolated | 16        | 2.25  | .46  | .41   | .38   | .37   |
| 755-4828  | 4116R-1-332       | 3.3K    | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4816  | 4116R-1-391       | 390     | Isolated | 16        | 2.25  | .45  | .41   | .38   | .37   |
| 755-4817  | 4116R-1-471       | 470     | Isolated | 16        | 2.25  | .48  | .44   | .40   | .39   |
| 755-4830  | 4116R-1-472       | 4.7K    | Isolated | 16        | 2.25  | .48  | .44   | .40   | .39   |
| 755-4819  | 4116R-1-681       | 680     | Isolated | 16        | 2.25  | .48  | .44   | .40   | .39   |
| 755-5021  | 4116R-2-102       | 1K      | Bussed   | 16        | 2.25  | .48  | .44   | .41   | .39   |
| 755-5034  | 4116R-2-103       | 10K     | Bussed   | 16        | 2.25  | .45  | .41   | .38   | .36   |
| 755-5026  | 4116R-2-222       | 2.2K    | Bussed   | 16        | 2.25  | .45  | .41   | .38   | .36   |
| 755-5030  | 4116R-2-472       | 4.7K    | Bussed   | 16        | 2.25  | .45  | .41   | .38   | .36   |
| 755-6021  | 4306R-101-102     | 1K      | Bussed   | 6         | 0.75  | .41  | .37   | .35   | .33   |
| 755-6034  | 4306R-101-103     | 10K     | Bussed   | 6         | 0.75  | .39  | .37   | .35   | .34   |
| 755-6030  | 4306R-101-472     | 4.7K    | Bussed   | 6         | 0.75  | .39  | .37   | .36   | .35   |
| 755-6121  | 4308R-101-102     | 1K      | Bussed   | 8         | 1.00  | .41  | .38   | .37   | .36   |
| 755-6134  | 4308R-101-103     | 10K     | Bussed   | 8         | 1.00  | .39  | .35   | .33   | .31   |
| 755-6126  | 4308R-101-222     | 2.2K    | Bussed   | 8         | 1.00  | .42  | .40   | .39   | .38   |
| 755-6117  | 4308R-101-471     | 470     | Bussed   | 8         | 1.00  | .42  | .37   | .35   | .33   |
| 755-6130  | 4308R-101-472     | 4.7K    | —        | 8         | 1.00  | .39  | .35   | .33   | .31   |
| 755-6421  | 4308R-102-102     | 1K      | Isolated | 8         | 1.00  | .43  | .39   | .36   | .34   |
| 755-6434  | 4308R-102-103     | 10K     | Isolated | 8         | 1.00  | .46  | .41   | .38   | .36   |
| 755-6447  | 4308R-102-104     | 100K    | Isolated | 8         | 1.00  | .43  | .39   | .36   | .34   |
| 755-6428  | 4308R-102-332     | 3.3K    | Isolated | 8         | 1.00  | .43  | .39   | .36   | .34   |
| 755-6625  | 4308R-104-221/331 | 220/330 | Dual     | 8         | 1.00  | .70  | .65   | .60   | .57   |
| 755-6221  | 4310R-101-102     | 1K      | Bussed   | 10        | 1.25  | .49  | .44   | .41   | .39   |
| 755-6234  | 4310R-101-103     | 10K     | Bussed   | 10        | 1.25  | .52  | .47   | .44   | .41   |
| 755-6247  | 4310R-101-104     | 100K    | Bussed   | 10        | 1.25  | .49  | .44   | .41   | .39   |

| Stock No. | Mfr.'s Type       | Ohms    | Circuit  | Pin Count | Watts | EACH |       |       |       |
|-----------|-------------------|---------|----------|-----------|-------|------|-------|-------|-------|
|           |                   |         |          |           |       | 1-9  | 10-24 | 25-49 | 50-99 |
| 755-6224  | 4310R-101-182     | 1.8K    | Bussed   | 10        | 1.25  | .49  | .44   | .41   | .39   |
| 755-6213  | 4310R-101-221     | 220     | Bussed   | 10        | 1.25  | .52  | .47   | .44   | .41   |
| 755-6226  | 4310R-101-222     | 2.2K    | Bussed   | 10        | 1.25  | .49  | .44   | .41   | .39   |
| 755-6215  | 4310R-101-331     | 330     | Bussed   | 10        | 1.25  | .52  | .47   | .44   | .41   |
| 755-6228  | 4310R-101-332     | 3.3K    | Bussed   | 10        | 1.25  | .52  | .47   | .44   | .41   |
| 755-6230  | 4310R-101-472     | 4.7K    | Bussed   | 10        | 1.25  | .49  | .44   | .41   | .39   |
| 755-6243  | 4310R-101-473     | 47K     | Bussed   | 10        | 1.25  | .52  | .47   | .44   | .41   |
| 755-6534  | 4310R-102-103     | 10K     | Bussed   | 10        | 1.25  | .49  | .44   | .41   | .39   |
| 755-6640  | 4310R-104-221/331 | 220/330 | Dual     | 10        | 1.25  | .82  | .65   | .59   | .54   |
| 755-4021  | 4606X-101-102     | 1K      | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4034  | 4606X-101-103     | 10K     | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4047  | 4606X-101-104     | 100K    | Bussed   | 6         | 0.75  | .26  | .21   | .20   | .19   |
| 755-4026  | 4606X-101-222     | 2.2K    | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4039  | 4606X-101-223     | 22K     | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4015  | 4606X-101-331     | 330     | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4017  | 4606X-101-471     | 470     | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4030  | 4606X-101-472     | 4.7K    | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4043  | 4606X-101-473     | 47K     | Bussed   | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4321  | 4606X-102-102     | 1K      | Isolated | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4334  | 4606X-102-103     | 10K     | Isolated | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4313  | 4606X-102-221     | 220     | Isolated | 6         | 0.75  | .33  | .26   | .24   | .22   |
| 755-4121  | 4608X-101-102     | 1K      | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4134  | 4608X-101-103     | 10K     | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4147  | 4608X-101-104     | 100K    | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4113  | 4608X-101-221     | 220     | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4126  | 4608X-101-222     | 2.2K    | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4139  | 4608X-101-223     | 22K     | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4115  | 4608X-101-331     | 330     | Bussed   | 8         | 1.00  | .29  | .24   | .22   | .21   |
| 755-4128  | 4608X-101-332     | 3.3K    | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4130  | 4608X-101-472     | 4.7K    | Bussed   | 8         | 1.00  | .29  | .24   | .22   | .21   |
| 755-4143  | 4608X-101-473     | 47K     | Bussed   | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4409  | 4608X-102-101     | 100     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4421  | 4608X-102-102     | 1K      | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4434  | 4608X-102-103     | 10K     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4447  | 4608X-102-104     | 100K    | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4459  | 4608X-102-105     | 1M      | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4410  | 4608X-102-121     | 120     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4425  | 4608X-102-202     | 2K      | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4426  | 4608X-102-222     | 2.2K    | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4439  | 4608X-102-223     | 22K     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4414  | 4608X-102-271     | 270     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4403  | 4608X-102-330     | 33      | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4415  | 4608X-102-331     | 330     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4405  | 4608X-102-470     | 47      | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4417  | 4608X-102-471     | 470     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4430  | 4608X-102-472     | 4.7K    | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4443  | 4608X-102-473     | 47K     | Isolated | 8         | 1.00  | .35  | .28   | .26   | .24   |
| 755-4209  | 4610X-101-101     | 100     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4221  | 4610X-101-102     | 1K      | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4234  | 4610X-101-103     | 10K     | Bussed   | 10        | 1.25  | .43  | .34   | .32   | .31   |
| 755-4247  | 4610X-101-104     | 100K    | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4236  | 4610X-101-203     | 20K     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4213  | 4610X-101-221     | 220     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4226  | 4610X-101-222     | 2.2K    | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4239  | 4610X-101-223     | 22K     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4227  | 4610X-101-272     | 2.7K    | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4215  | 4610X-101-331     | 330     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4228  | 4610X-101-332     | 3.3K    | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4217  | 4610X-101-471     | 470     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4230  | 4610X-101-472     | 4.7K    | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4243  | 4610X-101-473     | 47K     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4255  | 4610X-101-474     | 470K    | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4219  | 4610X-101-681     | 680     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4245  | 4610X-101-683     | 68K     | Bussed   | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4521  | 4610X-102-102     | 1K      | Isolated | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4534  | 4610X-102-103     | 10K     | Isolated | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4547  | 4610X-102-104     | 100K    | Isolated | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4503  | 4610X-102-330     | 33      | Isolated | 10        | 1.25  | .37  | .30   | .28   | .27   |
| 755-4530  | 4610X-102-472     | 4.7K    | Isolated | 10        | 1.25  | .37  | .30   | .28   | .27   |