

# ALUMINUM ELECTROLYTIC CAPACITORS

nichicon

**UG**

Chip Type, Higher Capacitance Range

series




For SMD



Anti-Solvent  
Feature  
(Through  
100V only)

- Chip Type, higher capacitance in larger case sizes ( $\phi 12.5$ ,  $\phi 16$ ,  $\phi 18$ ,  $\phi 20$ )
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape and tray.
- Compliant to the RoHS directive (2011/65/EU).




## Specifications


|                                                                             |                                                                                                                                                                                                                                        |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
|-----------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------------------------------------------------------------------------------------------------------------------|------|------|------|------|--------------------|------|---------------------------------------------------|------------|---------|
| Item                                                                        | Performance Characteristics                                                                                                                                                                                                            |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Category Temperature Range                                                  | -40 to +85°C                                                                                                                                                                                                                           |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Rated Voltage Range                                                         | 6.3 to 450V                                                                                                                                                                                                                            |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Rated Capacitance Range                                                     | 4.7 to 10000μF                                                                                                                                                                                                                         |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Capacitance Tolerance                                                       | ±20% at 120Hz, 20°C                                                                                                                                                                                                                    |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Leakage Current                                                             | Rated voltage (V)                                                                                                                                                                                                                      |                 | 6.3 to 100                                                                                                              |      |      |      |      |                    |      | 160 to 450                                        |            |         |
|                                                                             | —                                                                                                                                                                                                                                      |                 | After 1 minute's application of rated voltage, leakage current is not more than 0.03CV or 4 (μA), whichever is greater. |      |      |      |      |                    |      | I = 0.04CV+100 (μA) max. (1 minute's)             |            |         |
| Tangent of loss angle (tan δ)                                               | Measurement frequency : 120Hz at 20°C                                                                                                                                                                                                  |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
|                                                                             | Rated voltage (V)                                                                                                                                                                                                                      | 6.3             | 10                                                                                                                      | 16   | 25   | 35   | 50   | 63                 | 100  | 160 to 250                                        | 400・450    |         |
|                                                                             | tan δ (MAX.)                                                                                                                                                                                                                           | 0.28            | 0.24                                                                                                                    | 0.20 | 0.16 | 0.14 | 0.12 | 0.10               | 0.08 | 0.20                                              | 0.25       |         |
| For capacitance of more than 1000μF, add 0.02 for every increase of 1000μF. |                                                                                                                                                                                                                                        |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Stability at Low Temperature                                                | Measurement frequency: 120Hz                                                                                                                                                                                                           |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
|                                                                             | Rated voltage (V)                                                                                                                                                                                                                      |                 | 6.3                                                                                                                     | 10   | 16   | 25   | 35   | 50                 | 63   | 100                                               | 160 to 250 | 400・450 |
|                                                                             | Impedance ratio<br>ZT / Z20 (MAX.)                                                                                                                                                                                                     | Z-25°C / Z+20°C | 5                                                                                                                       | 4    | 3    | 2    | 2    | 2                  | 2    | 2                                                 | 3          | 6       |
|                                                                             |                                                                                                                                                                                                                                        |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Endurance                                                                   | The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.                                                                                    |                 |                                                                                                                         |      |      |      |      | Capacitance change |      | Within ±20% of the initial capacitance value      |            |         |
|                                                                             |                                                                                                                                                                                                                                        |                 |                                                                                                                         |      |      |      |      | tan δ              |      | 200% or less than the initial specified value     |            |         |
|                                                                             |                                                                                                                                                                                                                                        |                 |                                                                                                                         |      |      |      |      | Leakage current    |      | Less than or equal to the initial specified value |            |         |
| Shelf Life                                                                  | After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above. |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |
| Marking                                                                     | Black print on the case top.                                                                                                                                                                                                           |                 |                                                                                                                         |      |      |      |      |                    |      |                                                   |            |         |

## Chip Type

Type numbering system (Example : 50V 330 $\mu$ F)



|          | (mm)       |            |            |            |            |            |            |            |            |
|----------|------------|------------|------------|------------|------------|------------|------------|------------|------------|
| $\phi$ D | 12.5x13.5  | 12.5x16    | 12.5x21    | 16x16.5    | 16x21.5    | 18x16.5    | 18x21.5    | 20x16.5    | 20x21.5    |
| A        | 4.8        | 4.8        | 4.8        | 5.4        | 5.4        | 6.4        | 6.4        | 6.2        | 6.2        |
| B        | 13.6       | 13.6       | 13.6       | 17.1       | 17.1       | 19.1       | 19.1       | 21.1       | 21.1       |
| C        | 13.6       | 13.6       | 13.6       | 17.1       | 17.1       | 19.1       | 19.1       | 21.1       | 21.1       |
| E        | 4.0        | 4.0        | 4.0        | 6.3        | 6.3        | 6.3        | 6.3        | 8.8        | 8.8        |
| L        | 13.5       | 16.0       | 21.0       | 16.5       | 21.5       | 16.5       | 21.5       | 16.5       | 21.5       |
| H        | 1.0 to 1.4 | 1.0 to 1.4 | 1.0 to 1.4 | 1.0 to 1.4 | 1.0 to 1.4 | 1.0 to 1.4 | 1.0 to 1.4 | 1.3 to 1.7 | 1.3 to 1.7 |



※ The vibration structure-resistant product is also available upon request, please ask for details.

● Dimension table in next page.

CAT.8100D

## ■ Dimensions

| V            |      | 6.3         |      | 10          |      | 16          |      | 25          |      | 35          |      | 50          |      |
|--------------|------|-------------|------|-------------|------|-------------|------|-------------|------|-------------|------|-------------|------|
| (μF)<br>Cap. | Code | 0J          |      | 1A          |      | 1C          |      | 1E          |      | 1V          |      | 1H          |      |
| 220          | 221  |             |      |             |      |             |      |             |      |             |      | 12.5 × 13.5 | 450  |
| 330          | 331  |             |      |             |      |             |      |             |      |             |      | 12.5 × 13.5 | 520  |
| 470          | 471  |             |      |             |      |             |      | 12.5 × 13.5 | 550  | 12.5 × 13.5 | 580  | ● 16 × 16.5 | 740  |
| 1000         | 102  |             |      | 12.5 × 13.5 | 620  | 12.5 × 13.5 | 710  | 12.5 × 16   | 820  | ● 16 × 16.5 | 1000 | 18 × 21.5   | 1150 |
| 2200         | 222  | 12.5 × 16   | 890  | 12.5 × 16   | 960  | ● 16 × 16.5 | 1150 | △ 18 × 16.5 | 1350 | 18 × 21.5   | 1550 |             |      |
| 3300         | 332  | ● 16 × 16.5 | 1200 | 16 × 16.5   | 1300 | △ 18 × 16.5 | 1450 | 18 × 21.5   | 1700 |             |      |             |      |
| 4700         | 472  | 16 × 16.5   | 1400 | △ 18 × 16.5 | 1500 | 18 × 21.5   | 1750 |             |      |             |      |             |      |
| 6800         | 682  | △ 18 × 16.5 | 1650 | 18 × 21.5   | 1850 |             |      |             |      |             |      |             |      |
| 10000        | 103  | 18 × 21.5   | 2000 | □ 20 × 21.5 | 2200 |             |      |             |      |             |      |             |      |

| V            |      | 63          |     | 100         |     | 160         |     | 200         |     | 250         |     | 400         |     | 450                       |                 |
|--------------|------|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|---------------------------|-----------------|
| (μF)<br>Cap. | Code | 1J          |     | 2A          |     | 2C          |     | 2D          |     | 2E          |     | 2G          |     | 2W                        |                 |
| 4.7          | 4R7  |             |     |             |     |             |     |             |     |             |     | 12.5 × 13.5 | 115 | 12.5 × 13.5               | 115             |
| 10           | 100  |             |     |             |     |             |     |             |     | 12.5 × 13.5 | 150 | ● 16 × 16.5 | 140 | ● 16 × 16.5               | 140             |
| 22           | 220  |             |     |             |     |             |     | 12.5 × 13.5 | 235 | 12.5 × 16   | 240 | △ 18 × 16.5 | 280 | 16 × 21.5                 | 275             |
| 33           | 330  |             |     |             |     |             |     | 12.5 × 16   | 310 | ● 16 × 16.5 | 340 | 18 × 21.5   | 350 | 18 × 21.5                 | 345             |
| 47           | 470  |             |     |             |     | 12.5 × 16   | 370 | ● 16 × 16.5 | 415 | △ 18 × 16.5 | 415 | □ 20 × 21.5 | 430 |                           |                 |
| 68           | 680  |             |     | 12.5 × 13.5 | 350 | ● 16 × 16.5 | 500 | △ 18 × 16.5 | 505 | ★ 18 × 21.5 | 490 |             |     |                           |                 |
| 100          | 101  | 12.5 × 13.5 | 370 | 12.5 × 16   | 440 | △ 18 × 16.5 | 590 | 18 × 21.5   | 590 |             |     |             |     |                           |                 |
| 220          | 221  | 12.5 × 16   | 580 | △ 18 × 16.5 | 665 |             |     |             |     |             |     |             |     |                           |                 |
| 330          | 331  | ● 16 × 16.5 | 680 | 18 × 21.5   | 825 |             |     |             |     |             |     |             |     |                           |                 |
| 470          | 471  | △ 18 × 16.5 | 850 |             |     |             |     |             |     |             |     |             |     | Case size<br>φ D × L (mm) | Rated<br>ripple |

Size φ12.5×21 is available for capacitors marked, "●".

Size φ16×21.5L is available for capacitors marked, "△".

Size φ18×21.5L is available for capacitors marked, "□".

Size φ20×16.5L is available for capacitors marked, "★".

※ In this case, [6] will be put at 12th digit of type numbering system.

Rated ripple current (mA rms) at 85°C 120Hz

## ● Frequency coefficient of rated ripple current

| V          | Cap.(μF)      | Frequency | 50Hz | 120Hz | 300Hz | 1kHz | 10kHz or more |
|------------|---------------|-----------|------|-------|-------|------|---------------|
| 6.3 to 100 | 68            |           | 0.75 | 1.00  | 1.35  | 1.57 | 2.00          |
|            | 100 to 470    |           | 0.80 | 1.00  | 1.23  | 1.34 | 1.50          |
|            | 1000 to 10000 |           | 0.85 | 1.00  | 1.10  | 1.13 | 1.15          |
| 160 to 450 | 4.7 to 100    |           | 0.80 | 1.00  | 1.25  | 1.40 | 1.60          |

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please refer to page 3 for the minimum order quantity.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Nichicon:

[UUG1E102MNR1MS](#) [UUG1H102MNR1MS](#) [UUG1H221MNR1MS](#) [UUG1H331MNR1MS](#) [UUG1H471MNR1MS](#)  
[UUG1J101MNR1MS](#) [UUG1J221MNR1MS](#) [UUG1J331MNR1MS](#) [UUG1V102MNR1MS](#) [UUG2A101MNR1MS](#)  
[UUG2A680MNR1MS](#) [UUG2C101MNR1MS](#) [UUG2C470MNR1MS](#) [UUG2C470MNR1ZD](#) [UUG2D101MNR1MS](#)  
[UUG2D220MNR1MS](#) [UUG2D470MNR1MS](#) [UUG2E100MNR1MS](#) [UUG1J101MNL1MS](#) [UUG0J222MNL1MS](#)  
[UUG1H221MNL1MS](#) [UUG1J221MNL1MS](#) [UUG1J331MNL1MS](#) [UUG1V102MNL1MS](#) [UUG2A101MNL1MS](#)  
[UUG2A680MNL1MS](#) [UUG2D101MNL1MS](#) [UUG2D220MNL1MS](#) [UUG2D330MNL1MS](#) [UUG2D470MNL1MS](#)  
[UUG2E100MNL1MS](#) [UUG2G470MRL1MS](#) [UUG2G4R7MNL1MS](#) [UUG1V471MNL1MS](#) [UUG2A331MNL1MS](#)  
[UUG2E220MNR1MS](#) [UUG0J222MNL1ZD](#) [UUG0J332MNL6MS](#) [UUG0J332MNL6ZD](#) [UUG0J332MNL1MS](#)  
[UUG0J332MNL1ZD](#) [UUG0J472MNL1MS](#) [UUG0J472MNL1ZD](#) [UUG0J682MNL6MS](#) [UUG0J682MNL6ZD](#)  
[UUG0J682MNL1MS](#) [UUG0J682MNL1ZD](#) [UUG0J103MNL1MS](#) [UUG0J103MNL1ZD](#) [UUG1A102MNL1MS](#)  
[UUG1A102MNL1ZD](#) [UUG1A222MNL1MS](#) [UUG1A222MNL1ZD](#) [UUG1A332MNL1MS](#) [UUG1A332MNL1ZD](#)  
[UUG1A472MNL6MS](#) [UUG1A472MNL6ZD](#) [UUG1A472MNL1MS](#) [UUG1A472MNL1ZD](#) [UUG1A682MNL1MS](#)  
[UUG1A682MNL1ZD](#) [UUG1A103MRL1MS](#) [UUG1A103MRL1ZD](#) [UUG1C102MNL1MS](#) [UUG1C102MNL1ZD](#)  
[UUG1C222MNL6MS](#) [UUG1C222MNL6ZD](#) [UUG1C222MNL1MS](#) [UUG1C222MNL1ZD](#) [UUG1C332MNL6MS](#)  
[UUG1C332MNL6ZD](#) [UUG1C332MNL1MS](#) [UUG1C332MNL1ZD](#) [UUG1C472MNL1MS](#) [UUG1C472MNL1ZD](#)  
[UUG1E471MNL1MS](#) [UUG1E471MNL1ZD](#) [UUG1E102MNL1MS](#) [UUG1E102MNL1ZD](#) [UUG1E222MNL6MS](#)  
[UUG1E222MNL6ZD](#) [UUG1E222MNL1MS](#) [UUG1E222MNL1ZD](#) [UUG1E332MNL1MS](#) [UUG1E332MNL1ZD](#)  
[UUG1V471MNL1ZD](#) [UUG1V102MNL6MS](#) [UUG1V102MNL6ZD](#) [UUG1V102MNL1ZD](#) [UUG1V222MNL1MS](#)  
[UUG1V222MNL1ZD](#) [UUG1H221MNL1ZD](#) [UUG1H331MNL1ZD](#) [UUG1H471MNL6MS](#) [UUG1H471MNL6ZD](#)  
[UUG1H471MNL1MS](#) [UUG1H471MNL1ZD](#) [UUG1H102MNL1MS](#) [UUG1H102MNL1ZD](#) [UUG1J101MNL1ZD](#)