


4

3

2

1



4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


JUL ,2002.

© COPYRIGHT 2002 By -


ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J				SEE SHEET 1	


REFERENCE P.C. BOARD PATTERN LAYOUT (CONNECTOR MOUNTING SIDE)



REAL SIZE (SCALE 1:1)



1.8V	17.55	2.4	2.7
2.5V	18.45	1.5	1.8
POWER SUPPLY	D5	D4	D3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity		
DIMENSIONS: mm		CHK			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
			DDR1 & DDR2 SODIMM SOCKET		
			0.6mm PITCH 200POS		
			6.5 HEIGHT REVERSE TYPE		
MATERIAL	FINISH		SIZE	CAGE CODE	DRAWING NO
			A3	00779	C-1612773
CUSTOMER DRAWING		WEIGHT	RESTRICTED TO		
			SCALE	SHEET	REV
			2:1	2 OF 4	G2




2		1				
LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	-	SEE SHEET 1		-	-	-

D


C

B

A



A-A
SCALE 1:1
(180DEG. ROTATE)



B-B
SCALE 1:1

1. THE DIRECTION OF EACH CONNECTOR ON A TRAY IS REFERRED TO THIS DRAWING.
2. GENERAL TOLERANCE: ± 0.5

20EA/TRAY	5-1612773-4
20EA/TRAY	1-1612773-4
20EA/TRAY	1612773-4
20EA/TRAY	5-1612773-1
20EA/TRAY	1612773-1
QTY	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity		
DIMENSIONS: mm		CHK		NAME DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS 6.5 HEIGHT REVERSE TYPE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		SIZE A3		
0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$ FINISH		PRODUCT SPEC		CAGE CODE 00779		
MATERIAL		APPLICATION SPEC		DRAWING NO C-1612773		
		WEIGHT		RESTRICTED TO		
		CUSTOMER DRAWING		SCALE 1:2		
				SHEET 4 OF 4		
				REV G2		