

10mm BAYONET BASED LED LAMP


XYSG101W28V



SUN LED

Email : sales@us.sunled.com

Web Site : www.sunled.com



Notes:


1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01)$ unless otherwise noted.

Absolute maximum ratings (T _A =25°C)		SG (InGaAlP)	Unit
Reverse voltage	V _R	5	V
Forward voltage	V _F	32	V
Power dissipation	P _T	380	mW
Operating temperature	T _A	-40 ~ +70	°C
Storage temperature	T _{stg}	-40 ~ +85	

Operating Characteristics (T _A =25°C)		SG (InGaAlP)	Unit
Forward current (typ.) (V _F =28V)	I _F	10.8	mA
Reverse current (V _R =5V)	I _R	10	uA
Wavelength at peak emission (V _F =28V)	λ _{peak}	574	nm
Wavelength at Dominant emission (V _F =28V)	λ _D	568	nm
Spectral Line half-width (V _F =28V)	Δλ	26	nm

Part Number	Emitting Color	Emitting Material	Lens-color	Luminous Intensity (V=28V) mcd		Wavelength nm λ _P	Viewing Angle 2θ1/2
				min.	typ.		
XYSG101W28V	Green	InGaAlP	Water Clear	110	290	574	20°

XYSG101W28V



◆SG

