



REV	DOCUMENT	CHANGED BY	CHECK
B	0051698	MBN 29APR09	CMH



CHARACTERISTICS		
OPERATING FORCE ----- 30 OZ APPROX		
TOTAL TRAVEL ----- .100 APPROX		
ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT (2)		
LOAD	115 V 400 CYCLES	28 VDC
RESISTIVE	2.5 AMP	4 AMP
INDUCTIVE	2.5 AMP	2 AMP

DESIGN UNITS: INCH				DRAWN	SPK	29JUL08	Honeywell							
TOLERANCES UNLESS NOTED:				CHECK	KRB	29JUL08								
NO PLACES	X	±	0.400	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE PUSH BUTTON SWITCH							
ONE PLACE	.X	±	0.03											
TWO PLACE	.XX	±	0.015											
THREE PLACE	.XXX	±	0.005	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	CAGE CODE	DRAWING NAME		REV		
ANGLES	X	±	3.0°				B	I	-	702PB121		B		
THIRD ANGLE PROJECTION				RASTER			SCALE	NONE	WEIGHT: .070 LB MAX		SHEET	I	OF	I
														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[702PB121](#)