



0900-0



0900-0-00-00-00-00-11-0

Short stroke, Surface mount
Lowest profile

0900-1⇒4




0900-X-00-00-00-00-11-0

Standard stroke, Surface mount
Low profile

Basic Part Number	Length A
0900-1	.177
0900-2	.197
0900-3	.217
0900-4	.236


0905



0905-0-00-00-00-00-11-0

Standard stroke, Surface mount
Highest Profile

0907-X




0907-X-15-20-75-14-11-0

Standard stroke, Surface mount
High profile

Basic Part Number	Length A
0907-0	.255
0907-1	.275
0907-2	.295
0907-3	.315
0907-4	.335
0907-5	.350
0907-6	.370
0907-7	.390
0907-8	.410
0907-9	.430


0901



0901-0-00-00-00-00-11-0

Standard stroke
Solder mount in .027 min. mounting hole


0914



0914-0-15-20-77-14-11-0

Long stroke.
Solder mount in .027 min. mounting hole

0922




0922-0-15-20-75-14-11-0

Standard stroke

Solder mount in .027 min. mounting hole

0906-0




0906-0-15-20-76-14-11-0

Short stroke

Solder mount in .018 min. mounting hole

0906-1⇒4



0906-X-15-20-75-14-11-0

Standard stroke

Solder mount in .018 min. mounting hole

Basic Part Number	Length A
0906-1	.177
0906-2	.197
0906-3	.217
0906-4	.236

SPECIFICATIONS

SLEEVE & PLUNGER MATERIAL: Copper Alloy

SPRING MATERIAL: Beryllium Copper

CURRENT RATING: 2A continuous, 3A peak

CONTACT RESISTANCE: 20mΩ max.

DURABILITY: 1,000,000 cycles min.

DIMENSION IN INCHES

TOLERANCES ON: LENGTHS: ±.005

DIAMETERS: ±.002

ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - 20 - 7X - 14 - 11 - 0

BASIC PART #

SLEEVE & PLUNGER FINISH:

20 20μ" GOLD OVER NICKEL

SPRING FINISH:

14 10μ" GOLD OVER NICKEL

SPRING

75 Standard Stroke (.055):

76 Short Stroke (.039):

77 Long Stroke (.090):

25 grams@min stroke

60 grams@mid stroke

95 grams@max stroke

