




DESCRIPTION		
REV.	DATE	
A	06/29/04	UPDATE DRAWING FORMAT
B	03/27/05	ADD 17.5 HEX DIMNSION



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE .7mm
3. MAX. PANEL THICKNESS= 5.5mm

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		DO NOT SCALE DRAWING		CAD FILE		DWG. NO.		REV.		SIZE		SCALE	
8																	
7	FERRULE	COPPER	NICKEL	1	0.5 - 8mm ± 0.20mm	0.020 - .315 = ± 0.007"	APPROVALS	DATE									
6	HEX NUT	BRASS	NICKEL	1	8 - 30mm ± 0.40mm	.315 - 1.180 = ± 0.015"	DRAWN	G.R.S.	03/27/05								
5	LOCK WASHER	BRASS	NICKEL	1	30 - 120mm ± 0.50mm	1.180 - 4.724 = ± 0.020"	CHECKED										
4	GASKET	RUBBER	RED	1			ISSUED										
3	CONTACT PIN	BRASS	GOLD	1			SHEET	1	OF 1								
2	INSULATOR	DELIRIN	NATURAL	1													
1	BODY	BRASS	NICKEL	1													
DESCRIPTION		MATERIAL		FINISH		QTY		PART NO.		122370		REV. B		SIZE A		SCALE NA	