

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
				AB		REV PER ECR 08-003141	04FEB08	JR	TM
AMP WIRE RANGE		Listed FILE E13288		LR7189 Certified					
22-16 AWG SOLID OR STRANDED		22-16 AWG SOLID OR STRANDED		22-16 AWG SOLID OR STRANDED					

5.00 ±0.08 DIA
[.197 ±.003]
FOR #10 STUD

7.14
[.281]

0.79 MIN
[.031]

6.35 MIN
[.250]

16.61 MAX
[.654]

20.24 MAX
[.797]

1

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16

2 WIRE INSULATION DIA: 2.03-3.18 [.080-.125]

3 TONGUE MATERIAL THK: 0.79 ±0.05 [.031 ±.002]

4 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - VINYL, COLOR - RED

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02/11/93 DK SCHRUM		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 4/28/93 RE HERSEY	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD 4/28/93 DL MECKLEY	
FOR ORDER ENTRY		1-800-526-5142		MATERIAL - 4		FINISH TIN PLATE PER ASTM B545		PRODUCT SPEC 108-1034	
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				APPLICATION SPEC NOT AVAILABLE		NAME TERMINAL, RING TONGUE, P.I.D.G.	
						WEIGHT -		SIZE A3	
						CUSTOMER DRAWING		CAGE CODE 00779	
								DRAWING NO C-31884	
								RESTRICTED TO -	
								SCALE 4:1	
								SHEET 1 OF 1	
								REV AB	