



UNCONTROLLED DOCUMENT

PART NUMBER
SSB-COB15617SRW-AREV.
AREV. E.C.N. NUMBER AND REVISION COMMENTS
A E.C.N. #10926.DATE
11.06.02ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^{\circ}\text{C}$

PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		660		nm	
FORWARD VOLTAGE		3.4	4.4	V_f	
REVERSE VOLTAGE	8			V_r	$V_r=200\mu\text{A}$
LUMINOUS INTENSITY		200		cd/m^2	$I_f=560\text{mA}$
EMITTED COLOR:	RED				
REFLECTOR FINISH:	MILKY WHITE				

LIMITS OF SAFE OPERATION AT 25°C

PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT	700	mA
STEADY CURRENT	560	mA
POWER DISSIPATION	3.5	W
DERATE FROM 25°C	-25.8	$\text{mW}/^{\circ}\text{C}$
OPERATING TEMP.	-35 TO +80	$^{\circ}\text{C}$
STORAGE TEMP.	-40 TO +85	$^{\circ}\text{C}$
SOLDERING TEMP.	+260	$^{\circ}\text{C}$
2.0mm FROM BODY	3 SEC. MAX	

2 CHIPS IN SERIES
28 PARALLEL BRANCHES

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), XX=±0.5 (±0.020), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION -0.00 MAX.= +0.00 -DECIMAL PRECISION

REV.
APART NUMBER
SSB-COB15617SRW-A156mm x 17mm LCD BACKLIGHT, 660nm RED CHIPS,
MILKY WHITE REFLECTOR FINISH.

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

290 E. HELEN ROAD
PALATINE, IL 60067-6976
PHONE: +1.847.359.2790
US WEB: www.lumex.com
TW WEB: www.lumex.com.twDRAWN BY:
CT

CHECKED BY:

APPROVED BY:

DATE: 3.25.02
PAGE: 1 OF 1
SCALE: N/A