




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	01	REVISED	PER ECO-06-006293	16MAR06	JDP RW
		02	REVISED	PER ECO-09-024606	31OCT09	KK AEG

D




- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER. COLOR: NATURAL
- △ CONTACT MATERIAL: PHOSPHOR-BRONZE
- △ CONTACT FINISH:(A)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.00381 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- △ PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


C



B




Ø0.725±0.075
PLATED THROUGH HOLE
⊕ Ø0.15 (M)



RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)

A



0.51 REF
⊕ Ø0.20 (M) N P (M) R (M)

VIEW W-W
SCALE 20:1

5 OBSOLETE	94.00	47	95.88	192	5223660-8
	82.00	41	83.88	168	5223660-7
	70.00	35	71.88	144	5223660-6
5 OBSOLETE	58.00	29	59.88	120	5223660-5
	46.00	23	47.88	96	5223660-4
	34.00	17	35.88	72	5223660-3
5 OBSOLETE	22.00	11	23.88	48	5223660-2
	10.00	5	11.88	24	5223660-1
DIM C		B	DIM A	NUMBER OF SIGNAL POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER	16DEC04	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK R.WERTZ	16DEC04	NAME R.WERTZ	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	16DEC04	APPLICATION SPEC	
0 PLC ± -		APPLICATION SPEC	16DEC04	SIZE	
1 PLC ± -		APPLICATION SPEC	16DEC04	CAGE CODE	
2 PLC ± 0.13		APPLICATION SPEC	16DEC04	DRAWING NO	
3 PLC ± -		APPLICATION SPEC	16DEC04	RESTRICTED TO	
4 PLC ± -		APPLICATION SPEC	16DEC04	WEIGHT	
ANGLES ± -		APPLICATION SPEC	16DEC04	A1 00779	
FINISH		APPLICATION SPEC	16DEC04	5223660	
MATERIAL		APPLICATION SPEC	16DEC04	CUSTOMER DRAWING	
1		APPLICATION SPEC	16DEC04	SCALE 4:1	
2		APPLICATION SPEC	16DEC04	SHEET 1 OF 1	
3		APPLICATION SPEC	16DEC04	REV 02	