







N=Number of poles



| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
|                                                |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |

### Material

- Terminal body  
(metal housing): steel stamped
- Terminal screw: Steel Zinc plating "-" slot type
- Contacts: Brass
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

### Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:  
Solid wire(AWG): 12-22  
Stranded wire(AWG): 12-22
- Torque(Lb-In): 2.4
- Screw: M2.5
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

RoHS Compliant

PART NUMBER:

OSTTRXX2550

| No. of Poles | COLOR               |
|--------------|---------------------|
| 02: 2 Poles  | 0: Black            |
| 03: 3 Poles  | 5: Green (Standard) |
| ...          | 6: Blue             |
| 12: 12 Poles | 8: Grey             |



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

| TITLE                 | OSTTR 7.5 Series vertical (90D wire inlet) 2p-12p |                           |                           |              |                 |      |       |
|-----------------------|---------------------------------------------------|---------------------------|---------------------------|--------------|-----------------|------|-------|
| PART NO.              | OSTTRXX2550                                       |                           |                           | DWG NO.      | OSTTRXX2550.DWG |      |       |
| APPROVED              | CHECKED                                           | DESIGNED                  | DRAWN                     | CUST NO.     | Tolerance       |      |       |
| Shi Jun<br>2006.10.20 | Shi Jun<br>2006.10.20                             | xionghaitao<br>2006.10.20 | xionghaitao<br>2006.10.20 |              | UNIT: mm        | X.   | ±0.50 |
|                       |                                                   |                           |                           |              | SCALE: NONE     | X.X  | ±0.30 |
|                       |                                                   |                           |                           |              |                 | X.XX | ±0.10 |
|                       |                                                   |                           |                           |              |                 | X°   | ±1°   |
|                       |                                                   |                           |                           | SHEET: 01/01 | REV: E          |      |       |